


DATA SHEET DS/239	SI2KSYSUNO RIBBONS FOR SI2KPRINTUNO PRINTER			DATE 09/01/08
GRAPHIC REPRESENTATION				
				
REFERENCE ITEM CODE				
SI2KSBN/B - SI2KRBN/S - SI2KRBN/RS - SI2KRBN/L - SI2KRBN/R - SI2KRBN/W				
PHYSICAL PROPERTIES				
TEMPERATURE OF USE		+15 ÷ +32,5 °C, Relative humidity 10% ÷ 85%		
TEMPERATURE OF WAREHOUSING		+5 ÷ +32 °C, Relative humidity 10% ÷ 85%		
LIGH FASTNESS		Unaltered Black (≥ 7 – UNI 5773:1966 - Grey scale)		
ALCOHOL RESISTANCE		☺		
HEXANE RESISTANCE		☺		
SERIES PROPERTIES				
ITEMS CODE	RIBBON LENGHT	DESCRIPTION	COMPATIBILITY WITH SI2KPRINTUNO	
SI2KSBN/B	130	STRONG BLACK RIBBON	ALL FIRMWARE RELEASES	
SI2KRBN/R	130	RED RIBBON "PLATE" OPTION	ALL FIRMWARE RELEASES	
SI2KRBN/RS	130	RED RIBBON "STACK" OPTION	ALL FIRMWARE RELEASES	
SI2KRBN/W	110	WHITE RIBBON	ALL FIRMWARE RELEASES	
SI2KRBN/S	130	SILVER RIBBON	ALL FIRMWARE RELEASES	
SI2KRBN/L	130	GOLD RIBBON	ALL FIRMWARE RELEASES	
GENERAL CHARACTERISTICS				
PRINTABLE MATERIALS		SI2KPRINTUNO FEEDER OPTION		
ABS		'STACK FEEDER' (for cable tags)		
POLYCARBONATE		'SINGLE FEEDER' (for terminal block)		
PVC		'NONE' (for PVC items)		
METACRYLATE		'NONE' and 'ACRYLATE' for manual metacrylate items		
NOTES:				
Document Number	APPR. BY:	DATE:	REVISION OBJECT	PAGES:
78-8127-9039-8		09/01/08		1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[SI2KRBN/L](#) [SI2KRBN/R](#) [SI2KRBN/RS](#) [SI2KRBN/S](#) [SI2KRBN/W](#)