

## 3M™ Electrically Conductive Adhesive Transfer Tape 9709SL

### Product Description

3M™ Electrically Conductive Adhesive Transfer Tape 9709SL is an XYZ-electrically conductive pressure sensitive adhesive (PSA) conductive tape. 3M tape 9709SL consists of a unique conductive matrix (highly loaded silver based conductive fillers) that allows for an electrically conductive PSA for good grounding and attachment to desired surfaces. The product is an acrylic based adhesive solution and offers good adhesion and grounding performance to many surface types. 3M tape 9709SL helps improved electrical performance and reliable small size contacts in a thin format. It is useful for grounding, PSA attachment and EMI shielding designs.

### Key Features

- XYZ-conductivity through the adhesive
- Unique silver based fillers provide for unique grounding performance of flexible circuits
- Excellent conformability and quick bonding
- Good EMI shielding in bond line gap
- 50 µm thickness to conform to non-flat surfaces
- Unique acrylic formulation provides compatibility to many surface types
- Improved electrical contact to small size areas
- Good handling and workability
- 3M™ Electrically Conductive Adhesive Transfer Tape 9707 is the high adhesion version of 3M tape 9709SL (medium adhesion)
- 3M tape 9709SL uses premium low peel force release liners

### Product Construction / Materials Descriptions

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

3M™ Electrically Conductive Adhesive Transfer Tape 9709SL	
Property	Value
<b>Color</b> Face side Back side	Gold metallic Gold metallic
<b>Conductive Adhesive Type</b>	Acrylic conductive adhesive with silver based fillers
<b>Release Liner</b> Easy release side liner Tight release side liner	100 µm poly coated kraft (PCK) release liner 50 µm transparent PET release liner

# 3M™ Electrically Conductive Adhesive Transfer Tape 9709SL

## Typical Physical Properties and Performance Characteristics

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Final product specifications and testing methods will be outlined in the products Certificate of Analysis (COA) that is shipped with the commercialized product.


3M™ Electrically Conductive Adhesive Transfer Tape 9709SL		
Property	Target Value	Test Method
Thickness	50 µm	ASTM D1000 <sup>a</sup>
Adhesion to Stainless Steel	825 gf/inch	ASTM D1000 <sup>a</sup>
Electrical Resistance through Z-axis	0.2 Ω	3M ETM-12 <sup>b</sup>

<sup>a</sup> Tested in accordance with modified ASTM D1000 test method.

<sup>b</sup> 3M test methods as described below.

### ETM-12: Z-Axis Electrical Resistance through Adhesive<sup>b</sup>

Place conductive tape pieces in 10 mm x 10 mm on the center of the electrodes on 3M ETM-7 testing board. Then place 3M ETM-12 testing board with the gold plated side down on the tapes between electrodes. After initial hand lamination to provide for a 10 mm x 10 mm contact area between the tapes and electrodes, apply 2kg rubber roller across the tape one time. Application method simulates a typical manufacturing process that might be used to apply the tapes to a surface. After 20 minutes of dwell time, the DC resistance between the electrodes are measured with a micro-ohm meter. The resistance results are recorded after 5 ~ 30 seconds for initial resistance.



## Shielding Effectiveness

Many factors determine the shielding effectiveness of a conductive adhesive tape, including type and thickness of the conductive layers, adhesive strength, degree of contact, smoothness of application surface and test frequency. For 3M™ Electrically Conductive Adhesive Transfer Tape 9709SL, the typical shielding effectiveness is expected to be in the range of 30 dB to 50 dB, using a standard EMI shielding test methods and through the thickness of the sample tested.

## Applications

3M™ Electrically Conductive Adhesive Transfer Tape 9709SL is typically used for applications requiring excellent electrical conductivity from the application substrate through the adhesive to a second substrate. Common uses include grounding and EMI shielding in equipment and components.

# 3M™ Electrically Conductive Adhesive Transfer Tape 9709SL

## End Use Application Techniques

**Note:** Carefully read and follow the manufacturer's precautions and directions for use when working with solvents. Tape application below 10°C (50°F) is not suggested. Once properly applied, low temperature holding power is generally satisfactory.

The 3M™ Electrically Conductive Adhesive Transfer Tape bond strength depends on the amount of adhesive-to-surface contact developed during application and substrate type and surface conditions.

1. Firm application pressure helps develop better wet-out and adhesive contact and may lead to improved bond strength as well as electrical conductivity. Pressure must be applied to the bond area after assembly to ensure sufficient wet-out of the 3M tape 9709SL adhesive to the substrates and to engage the conductive acrylic adhesive fillers with the substrates to make electrical connection. Mechanical pressure (roller, metal bar) or finger pressure at 5-15 psi. (Optimally the application conditions are determined via a set of Design of Experiments (DOE) using a range of application pressures, dwell time and temperatures (suggested initial range might include 5-15 psi, 2-5 seconds, 21°C-38°C).
2. Heat may be applied simultaneously with pressure to improve wetting, final bond strength and electrical conductivity. Suggested temperature range to evaluate is in the 38°C-60°C range.
3. To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.

## Storage and Shelf Life

The shelf life of 3M™ Electrically Conductive Adhesive Transfer Tape 9709SL is 12 months from the date of manufacture when stored in roll form, in the original packaging materials, and stored at 21°C (70°F) and 50% relative humidity.

## Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is commercially available from 3M. The commercially available product will have a COA specification established. The COA contains the 3M specifications and test methods for the products performance limits that the product will be supplied against. The 3M product is supplied to 3M COA test specifications and the COA test methods. Contact your local 3M representative for this product's COA.

This technical data sheet may contain preliminary data and may not match the COA specification limits and/or test methods that may be used for COA purposes.

Final product specifications and testing methods will be outlined in the products Certificate of Analysis (COA) that is shipped with the commercialized product.

# 3M™ Electrically Conductive Adhesive Transfer Tape 9709SL

**Regulatory:** For regulatory information about this product, contact your 3M representative.

**Technical Information:** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

**Warranty, Limited Remedy, and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M Product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



## Electronics Materials Solutions Division

3M Center, Building 224-3N-11  
St. Paul, MN 55144-1000  
1-800-251-8634 phone  
651-778-4244 fax  
[www.3M.com/electronics](http://www.3M.com/electronics)

3M is a trademark of 3M Company.  
Please recycle.  
©3M 2016. All rights reserved.  
60-5002-0984-0

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)  
[9709SL](#)