Joint Design for Structural Adhesives

Technical Bulletin

November 2017

Joint design – Specific stress resistance is a major consideration.

Joints should be specifically designed for use with structural adhesives. This is largely a matter of common sense and experience. Two basic factors should be the design guidelines. First, structural joints should be designed so that all of the bonded area equally shares the load. Second, the joint configuration should be designed so that basic stress is primarily in shear of tensile, with cleavage and peel minimized oreliminated. Finally, appropriate joint thickness should be accounted for in the design (typically, 0.1-0.5mm depending on joint design and stresses, temperature fluctuations during use, etc).

The following structural joints and their advantages/disadvantages illustrate some typical design alternatives. They are not, of course, the limit of possible adhesive bonded joints.

Lap joints ...

... are most common. They are most practical and applicable in bonding thin materials.

The *simple lap joint* is off-set. This can result in cleavage and peel stress under load when using thin materials.

The *joggle lap joint* gives more uniform stress distribution than either the simple or tapered lap joint. The joint can be formed by simple metal forming operations. The curing pressure is easily applied.

A *tapered single lap joint* is more efficient than a simple lap joint. The tapered edge allows bending of the joint edge under stress.

The *double butt lap joint* gives more uniform stress distribution in the load-bearing area than the above joints. However, this type of joint requires machining which is not always feasible with thinner gauge metals.

Double scarf lap joints have better resistance to bending forces than double butt joints. However, this type of joint also requires machining.

Angle joints ...

... give rise to either peel or cleavage stress depending on the gauge metal. Typical approaches to the reduction of cleavage are illustrated.

Butt joints ...

A straight butt joint has poor resistance to cleavage. The following recessed butt joints are recommended: landed scarf tongue and groove, conventional tongue and groove, and scarf tongue and groove. Landed scarf tongue and groove joints act as stops which can control adhesive line thickness. Tongue and groove are self- aligning during assembly and act as a reservoir for void filling type adhesives.



Technical Bulletin Joint Design for Structural Adhesives

Cylindrical Joints

The T-joint and overlap slip joint are typical for bonding cylindrical parts such as tubing, bushings, and shafts. With adhesive bonding, all available contact area contributes to carrying the load. Adhesives also provide a joint with better appearance and eliminate distortion caused by high welding temperatures.

Corner joints - sheet metal

Corner joints can be assembled with adhesives by using simple supplementary attachments. This permits joining and sealing in a single operation. Typical designs are right angle butt joints, slip joints and right angle support joints. These joints increase the structure's rigidity. Void filling adhesives are most frequently used. Use of a heat curing adhesive depends on the heat resistance of the materials being bonded.

With this technique, thin gauge metals or sandwich panels can be easily formed into boxes, cases, housings, vehicle bodies, metal boat hulls, etc.

Corner joints - Rigid members

Corner joints, as in storm doors or decorative frames, can be adhesive bonded. End lap joints are the simplest design type although they require machining. Adhesives requiring pressure during cure may be utilized in such designs. Mortise and tenon joints are excellent from a design standpoint but also require machining. Mitered joint with spline is best if members are hollow extrusions. In this case, a void filling adhesive is recommended.

Stiffener Joints

Deflection and flutter of thin metal sheets can be minimized with adhesive bonded stiffeners. When such assemblies are flexed, peel stresses are exerted on the adhesive. If the flanges on the stiffening section can bend with the sheet, minimum peel stress on the bond will result. Increasing sheet gauge or decreasing the gauge of the stiffener flange will give equivalent results. Stiffening members such as T-sections, hat sections and corrugated backing can be used depending on desired rigidity.



Technical Bulletin Joint Design for Structural Adhesives

Technical Information	The technical information, recommendations, and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted.



Industrial Adhesives and Tapes Division 3M Center, Building 225-3S-06 St. Paul, MN 55144-1000 800-362-3550 • 877-369-2923 (Fax) www.3M.com/structuraladhesives 3M is a trademark of 3M Company.

©3M 2017 78-6900-9939-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

<u>3M</u>:

<u>9140</u> DP42	<u>20</u> <u>3535</u> <u>3501</u>	<u>1751</u> DP80	10NS <u>3549</u>	1838L 3532	7100148758	7000036224	7000046634
700000897	700000861	700000874	700000875	700000895	700000896	7000028577	7000046328
7000046360	7000046480	7000046481	7000046485	7000046642	7000046650	7000121212	7000121318
7000121321	7000148268	7000148270	7010130543	7010130544	7010170293	7010170296	7010295295
7010295349	7010309749	7010309882	7010310199	7010310208	7010329534	7010329537	7010329538
7010329704	7010329707	7010330216	7010330223	7010330477	7010365926	7010366123	7010366158
7010366160	7010366542	7010367262	7010367265	7010367414	7010409611	7010412194	7010412243
7010415316	7100007956	7100009581	7100010271	7100010680	7100014024	7100015959	7100024045
7100024055	7100036719	7100036721	7100036943	7100039206	7100039208	7100039230	7100039240
7100039250	7100039251	7100039254	7100039255	7100039260	7100039262	7100039264	7100039269
7100041737	7100041738	7100049744	7100067297	7100069441	7100069452	7100069498	7100076677
7100077148	7100078165	7100078166	7100082563	7100088846	7100089475	7100097636	7100143701