




3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



NOTES:


1. MATERIALS:
- | | | |
|--------------|---------------|---------------|
| SPRINGS | SS | |
| CONTACTS | Be Cu | PLATING : Au |
| IC GUIDES | PES | COLOR : BLACK |
| PRESSURE PAD | PES | COLOR : BLACK |
| COVER | PPS or equiv. | COLOR : BLACK |
| BASE | PES | COLOR : BLACK |
2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).
3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE: WWW.3MCONNECTOR.COM PN 240-4205-01

DESIGN REFERENCE				NEXT ASSEMBLY				A		37213		INITIAL RELEASE				ARM			
DISTRIBUTION CODES								REV		ECO		ISSUE DATE AND DESCRIPTION				DRFT		CHKD	
								DRFT		DATE				MFG		DATE			
								CHKD		DATE				APPVL		DATE			
DIVISION				DIVISION CODE				3M 3M Center St. Paul, MN 55144				© 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.							
DO NOT SCALE DRAWING				SCALE 5 1												TOLERANCES EXCEPT AS NOTED			
				INCHES															
				THIRD ANGLE PROJECTION															
INTERPRET PER ASME Y14.5 - 1994				MILLIMETERS				TITLE QFN TEST SOCKET, 0.4mm 40 POS, EVEN ROW, 5X5 PKG WITH TP											
MAX SURFACE ROUGHNESS				CAGE NUMBER															
125 ✓ ☒ MARKED ONLY				SIZE C															
				DRAWING NO. 78-5100-2483-5				REV. A											
				MODEL				TEXTTOOL - QFN				DET. LISTS ☐ YES ☒ NO							
				ANGLES ± 1°				SHT 1 OF 2											

[illegible]

DETAIL D

DETAIL E

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD	
DISTRIBUTION CODES				DRFT	DATE		MFG	DATE		
				CHKD	DATE		APPVL	DATE		
DIVISION		DIVISION CODE		 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.						
DO NOT SCALE DRAWING	SCALE 5 1	TOLERANCES EXCEPT AS NOTED				TITLE QFN TEST SOCKET, 0.4mm 40 POS, EVEN ROW, 5X5 PKG WITH TP				
		INCHES .0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002								
THIRD ANGLE PROJECTION		MILLIMETERS 0 ± .0 ± .00 ± .000 ±								
INTERPRET PER ASME Y14.5 - 1994										
MAX SURFACE ROUGHNESS				CAGE NUMBER	SIZE	DRAWING NO.		REV.		
125	☐ ALL SURFACES ☒ MARKED ONLY	ANGLES ± 1°				78-5100-2483-5		A		
				MODEL		TEXTTOOL - OFN		DET. LISTS	☐ YES ☒ NO	SHT 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[240-4205-01](#)