



Heat Shrink Tubing Selection Guide

HEAT SHRINK TUBING



3M™ Heat Shrink Tubing Selection Guide

PRODUCT	MATERIAL/ TYPICAL APPLICATIONS	OPERATING TEMPERATURE RANGE	SHRINK TEMP. (Min.)	SHRINK RATIO	STANDARD SIZES EXPANDED DIAMETER	DIELECTRIC STRENGTH (V/mil)	VOLUME RESISTIVITY (ohm-cm)	TENSILE STRENGTH (PSI)
Single-Wall Polyolefin Tubing								
FP-301	Flexible Polyolefin General purpose flame retardant insulation for UL, CSA and MIL-DTL-23053/5 applications; cable and component covering. Class 1 = opaque colors; Class 2 = clear.	-55°C to +135°C	212°F 100°C	2:1	3/64" to 4"	900	10 ¹⁵	2400
FP-301VW	Highly Flame-Retardant, Flexible Polyolefin Insulation applications, flame-retardant applications requiring UL VW-1 and CSA OFT, fire-resistant wiring.	-55°C to +135°C	212°F 100°C	2:1	3/64" to 4"	900	10 ¹⁵	2400
VFP-876	Very Flexible Polyolefin Terminal insulation, low shrink-temperature applications.	-55°C to +135°C	212°F 100°C	2:1	3/64" to 2"	800	10 ¹⁴	2100
SFTW-203	Very Flexible Polyolefin Shrink-fit jacketing and insulation of flexible wire bundles and temperature-sensitive components.	-55°C to +135°C	212°F 100°C	3:1	1/16" to 1 1/2"	700	10 ¹⁵	2600
SFTW-202 GYS	Green and Yellow Striped , 2:1 very flexible polyolefin, primarily used for ground wire identification.	-55°C to +135°C	212°F 100°C	2:1	1/8" to 3/4"	700	10 ¹⁴	2600
CP-221	Commercial Grade Polyolefin Terminal strip wire markers and general purpose insulation.	-55°C to +125°C	250°F 121°C	2:1	3/64" to 2"	550	10 ¹⁴	1800
Adhesive-Lined, Polyolefin Tubing								
MW	Multiple Wall Polyolefin Insulation, strain relief and sealing of electrical connections, wire splices and components.	-55°C to +110°C	275°F 135°C	2.5:1	1/8" to 1"	900	10 ¹⁵	2200
EPS-200	Environmental Protection Sleeve Insulation, strain relief and environmental protection of electrical wire bundles and components.	-55°C to +110°C	250°F 121°C	2:1	1/8" to 2"	800	10 ¹⁴	2100
EPS-300	Environmental Protection Sleeve Insulation, strain relief and environmental protection for automotive and marine wire bundles and splices.	-55°C to +110°C	250°F 121°C	3:1	1/8" to 1-1/2"	700	10 ¹⁴	2100
EPS-400	Environmental Protection Sleeve Insulation, strain relief and environmental protection for sealing voids in multiple wire bundles for automotive and marine applications.	-55°C to +110°C	250°F 121°C	4:1	.300" to .700"	700	10 ¹⁴	1900
TMW	Semi-Rigid Multiple Wall Terminal Protection Sleeve Insulation, strain relief and environmental protection. Uses include the manufacture of heat shrink butt connectors, ring terminals and fork terminals.	-55°C to +110°C	275°F 135°C		.183" to .330"	900	10 ¹⁴	2500
TES SMS	All-Weather, Heat-Shrinkable, Dual Wall, Polyolefin Tubing for Automotive Wire Harnesses	-55°C to +110°C	250°F 121°C	4:1 4:1	.220" to .700"	500	10 ¹⁴	2450 1900
Special Purpose Tubing								
KYNAR®	Polyvinylidene Fluoride Heat-resistant transparent insulation and marking for electronic and appliance applications.	-55°C to +175°C	347°F 175°C	2:1	3/64" to 2"	900	10 ¹⁴	5500
NST	Modified Neoprene Insulation and abrasion resistant covering of wiring and cable harnesses. Oil resistant coverings.	-70°C to +121°C	275°F 135°C	2:1	1/8" to 3"	800	10 ¹²	2100
VTN-200	Fluoroelastomer Synthetic fuel and hydraulic oil resistant applications, high-temperature coverings.	-55°C to +200°C	347°F 175°C	2:1	1/8" to 2"	500	10 ¹²	2400
PSTH	Flexible Elastomeric Polyester Designed for harsh operating conditions.	-55°C to +150°C	338°F 170°C	2:1	3/16" to 2 1/2"	500	10 ¹⁴	2200
Heavy-Duty Tubing								
MDT	Medium-Duty Excellent abrasion, corrosion and environmental protection. Flame retardant.	-55°C to +110°C	250°F 121°C	3:1	.400" to 4.30"	500	10 ¹⁴	2400
HDT	Heavy-Duty Fabricated from specially formulated cross-linked polyolefin, assuring long-term environmental protection. Highly chemical, abrasion and split resistant.	-55°C to +110°C	250°F 121°C	3:1	.300" to 7.00"	500	10 ¹⁴	2400
CCT	Adhesive-lined , 3:1 flexible polyolefin for sealing and insulating CATV connections.	-55°C to +110°C	250°F 121°C	3:1	.400" to 3.00"	500	10 ¹⁴	2000
BBI	Bus Bar Tubing , Designed for insulating rectangular, square, or round bus bar rated 5 kV through 35 kV.	-55°C to +110°C	250°F 121°C		2.38" to 10.28"	550	10 ¹³	2200

ULTIMATE ELONGATION (%)	LONGITUDINAL CHANGE (± %)	SPECIFIC GRAVITY	FLAMMABILITY	CORROSIVE EFFECT	ABRASION RESISTANCE	FLEXIBILITY (See Note below)	FUEL & OIL RESISTANCE	SOLVENT RESISTANCE	RESISTANCE TO ACIDS AND ALKALIS	APPLICABLE SPECIFICATIONS
400	5	1.3	Self-Extinguish meets UL 224 All-Tubing Flame Test (except clear)	Non-Corrosive	Good	3	Good	Exc.	Exc.	MIL-DTL-23053/5, Class 1, 2; AMS-3636 & 3637; UL File E-39100; CSA LR38227; ABS
400	+1, -10	1.5	Self-Extinguish meets UL 224 VW-1 Test	Non-Corrosive	Good	3	Good	Exc.	Exc.	MIL-DTL-23053/5, Class 3; UL File E-39100, VW-1; CSA LR38227, OFT
450	5	1.3	Self-Extinguish meets UL 224 All-Tubing Flame Test	Non-Corrosive	Good	2	Good	Exc.	Exc.	MIL-R-46846, Type V; UL File E-39100; CSA LR38227, MIL-DTL-23053/5
400	5	1.29	Self-Extinguish	Non-Corrosive	Good	3	Good	Good	Exc.	MIL-DTL-23053/5*, Class 1; UL File E-48398; CSA LR38227
400	5	1.29	Self-Extinguish	Non-Corrosive	Good	3	Good	Good	Exc.	MIL-DTL-23053/5, Class 1; UL File E-48398; CSA LR38227
400	5	1.1	Self-Extinguish	Non-Corrosive	Good	4	Good	Good	Exc.	
400	+1, -10	1.0	Non-Flame Retardant	Non-Corrosive	Good	7	Good	Good	Exc.	MIL-DTL-23053/4, Class 1; AMS-3634; UL File E-157227
450	+1, -5	1.3	Self-Extinguish meets UL 224 All-Tubing Flame Test (jacket)	Non-Corrosive	Good	3	Good	Good	Exc.	MIL-DTL-23053/4, Class 2; UL File E-39100
450	+1, -15	1.3	Self-Extinguish meets UL 224 All-Tubing Flame Test (jacket)	Non-Corrosive	Good	3	Good	Good	Exc.	MIL-DTL-23053/4, Class 3; UL File E-157227; ABS
400	+1, -10	1.25	Self-Extinguish	Non-Corrosive	Good	7	Good	Good	Exc.	UL File E-157227
400	+1, -10	1.0	Non-Flame Retardant	Non-Corrosive	Good	7	Good	Good	Exc.	UL File E-157227
450 350	+0, -10 +0, -10	0.97 1.25	TES Non-Flame Retardant SMS Self-Extinguish	Non-Corrosive Non-Corrosive	Good Good	TES 5 SMS 3	Good Good	Good Good	Exc. Exc.	ESB-M99D56-Ford MS-DB56-Chrysler
350	+1, -10	1.7	Self-Extinguish meets UL 224 VW-1 Test	Non-Corrosive	Exc.	10	Exc.	Exc.	Exc.	MIL-DTL-23053/18, Class 1; MIL-DTL- 23053/8; AMS-3632; UL File E-39100, VW-1, E69751; CSA LR38227 OFT
500	+1, -10	1.3	Self-Extinguish	Non-Corrosive	Exc.	1	Exc.	Good	Exc.	MIL-R-46846, Type I, Class 1; MIL-DTL-23053/1, Class 1, 2; AMS-3623, SC-X-15112
450	+1, -10	1.7	Self-Extinguish	Non-Corrosive	Exc.	4	Exc.	Exc.	Exc.	MIL-R-46846, Type III, Class 1; MIL-DTL-23053/13
350	+2, -8	1.6	Self-Extinguish	Non-Corrosive	Exc.	4	Exc.	Exc.	Exc.	SC-X15111C; meets the functional requirements of MIL-DTL-23053/16
475	+1, -10	1.28	Self-Extinguish	Non-Corrosive	Good	8	Good	Good	Exc.	MIL-DTL-23053/15, Class 2; ABS
475	+1, -10	1.28	Self-Extinguish	Non-Corrosive	Good	9	Good	Good	Exc.	MIL-DTL-23053/15, Class 1; ABS
400	+1, -10	1.30	Self-Extinguish	Non-Corrosive	Good	8	Good	Good	Exc.	
575	+0, -10	1.20	Self-Extinguish	Non-Corrosive	Good	8	Good	Good	Exc.	ASTM-D-257, 149, 150, 2303; IEC 216; ANSI/IEEE Std C37.20

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability.

3M's product warranty is stated in its Product Literature available upon request. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated

above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800 676 8381
Fax 800 828 9329
<http://www.3M.com/electrical>



40% Pre-consumer waste paper
10% Post-consumer waste paper

Litho in USA.

© 3M 2004 80-6109-4340-1B(1092.0)W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[FP-301-VW-1-Black](#) [SFTW-203-1/16-48-Black](#) [SFTW-203-1/8-48-Black](#) [SFTW-203-1/4-48-Black](#) [SFTW-203-1/4-Black](#) [SFTW-203-3/8-48-Black](#) [SFTW-203-3/8-Black](#) [SFTW-203-1/2-48-Black](#) [SFTW-203-3/4-48-Black](#) [SFTW-203-3/4-Black](#) [SFTW-203-1 1/2-Black](#) [SFTW-203-1-48-BLACK](#) [SFTW-203-1-1/2-48-Black](#) [FP-301-VW-1 1/2-Black](#) [FP-301-VW-3/32-Black](#) [FP-301-VW-3/16-Black](#) [FP-301-VW-3/4-Black](#) [FP-301-VW-3-Black](#) [FP-301-VW-1/4-Black](#) [FP-301-VW-3/8-Black](#) [FP-301-VW-2-Black](#) [FPVW-1 1/2-48"-Black-Bulk](#) [FPVW-1/8-48"-Black](#) [FPVW-1/8-48"-Black-Bulk](#) [FPVW-1-48"-Black](#) [FPVW-2-48"-Black](#) [FPVW-2-48"-Black-Bulk](#) [FPVW-3/8-48"-Black-Bulk](#) [FPVW-3/32-48"-Black](#) [FPVW-3/32-48"-Black-Bulk](#) [FPVW-3-48"-Black](#) [FPVW-3-48"-Black-Bulk](#)