




Water Contact Indicator Tape 5557

Clear evidence of water damage to assist warranty claim resolution

When water contacts the edges of this tape, the tape color changes permanently from white to red. In electronic products ranging from mobile phones to MP3 players, you'll have clear evidence of water contact without false identification from high humidity.



*Indicator layer and polyester liner combine for easy and accurate die-cutting, including **high efficiency rotary**.*

Each layer of this multiple layer tape is engineered for specific performance.

Indicator layer:

- Absorbs water quickly and draws up color to be visible through transparent top film
- Withstands heat and humidity without changing color

Transparent PET top film:

- Thermal, flexographic, and screen print images on film show against white backing

- Protects indicator layer from soiling and moisture during handling

3M™ acrylic adhesive:

- Resists UV, chemicals, and temperature
- Bonds with high strength to most substrates including low surface energy plastics such as polypropylene and powder coatings


Polyester liner:

- Combines with indicator layer for die-cutting ease and accuracy

Application ideas:

- Mobile phones
- PDAs, personal communicators, and pagers
- MP3, game, and CD players
- 2-way radios and cordless phones
- Digital, film, and video cameras
- Laptop computers and keyboards
- Li-MH batteries and chargers
- Other portable electronic devices

3M™ Water Contact Indicator Tape 5557



Product Construction

Top Film	Backing	Adhesive	Color	Standard Roll Length
Polyester	Indicator Layer	Acrylic	White	12" x 180 yds

Typical Physical Properties

Adhesion, ozs/in (ASTM-D3330, 90° Peel Adhesion, 72 hr dwell)
 Stainless Steel: 82 ozs/in (88 N/100 mm)
 Polycarbonate: 47 ozs/in (52 N/100 mm)

Thickness (ASTM D-3652):

Tape: 0.0090" (0.229 mm)
 Release Liner: 0.0020" (0.051 mm)

Humidity Resistance¹ (55°C, 95% R.H.)

0 hrs exposure 7 days After water contact



¹Tape is applied to polycarbonate panel and hung vertically in heat/humidity chamber.

Note: The above technical information and data should be considered representative or typical only and should not be used for specification purposes.

For additional product information or sales assistance, contact:

ASIA PACIFIC	Phone Number	Website
3M Asia Pacific Pte Ltd	65-450-8816	
3M Australia Pty, Ltd	61-2-9833-5333	www.3m.com/au
3M China Limited	86-21-6275-3535	www.3m.com/cn
3M Hong Kong Limited	852-2806-6387	www.3m.com/hk
Japan - Sumitomo 3M Limited	81-3-3709-8261	www.mmm.co.jp
3M Korea Limited	82-2-3771-4030	www.3m.co.kr
3M Malaysia Sdn. Berhad	60-3-7806-3653	www.3m.com/intl/my
3M New Zealand Limited	64-9-444-4760	www.3m.com/nz
3M Philippines Inc.	63-2-813-3781	www.3m.com/ph
3M Singapore	65-454-8611	www.3m.com/sg
3M Taiwan Limited	886-2-2704-9011 ext. 318	www.3m.com/tw
3M Thailand Limited	66-2-260-8577 ext. 302	www.3m.com/th
NORTH AMERICA	Phone Number	Website
3M Canada	519-451-2500	www.3m.com/ca
	1-800-364-3577	
3M Mexico	52-52-70-04-00	www.3m.com/mx
3M USA	651-737-6501	www.3m.com/eadhesives
	1-800-364-3577	

EUROPE	Phone Number	Website
3M Austria	43-1-866860	www.3m.com/at
3M Belgium	32-2-7225111	www.3m.com/be
3M Czech Republic	420-2-61380111	www.3m.com/cz
3M Denmark	45-43-480100	www.3m.com/dk
3M East	41-41-7994040	www.3m.com/ch
3M Finland	358-9-5252452	www.3m.com/fi
3M France	33-1-30-316161	www.3m.com/fr
3M Germany	49-2131-140	www.3m.com/de
3M Ireland	353-1-2803555	www.3m.com/ie
3M Israel	972-9-9561490	
3M Netherlands	31-71-5450450	www.3m.com/nl
3M Norway	47-63-847500	www.3m.com/no
3M Spain	34-91-3216000	www.3m.com/es
3M Sweden	46-8-922100	www.3m.com/se
3M Switzerland	41-1-7249090	www.3m.com/ch
United Kingdom	44-870-6080-050	www.3m.com/uk

IMPORTANT NOTICE: 3M MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of application. Please remember that many factors can affect the use and performance of a 3M product in a particular application. The materials to be bonded with the product, the surface preparation of those materials, the product selected for use, the conditions in which the product is used, and the time and environmental conditions in which the product is expected to perform are among the many factors that can affect the use and performance of a 3M product. Given the variety of factors that can affect the use and performance of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

LIMITATION OF REMEDIES AND LIABILITY: If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M shall not otherwise be liable for any loss or damages, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including but not limited to contract, negligence, warranty, or strict liability.



Industrial Markets

3M Center
 St. Paul, MN 55144-1000
www.3M.com/eadhesives



40% Pre-consumer waste paper
 10% Post-consumer waste paper

Printed in U.S.A.
 © 3M 2002
 78-9236-7071-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)
[5557](#)