# 3M<sup>TM</sup> Scotchcast<sup>TM</sup> Flexible Power Cable Splicing Kits 82-F and 82-BF Series

Data Sheet	September 2012			
Description	3M <sup>™</sup> Scotchcast <sup>™</sup> Flexible Power Cable Splicing Kits 82-F and 82-BF Series are flexible inline and tap splices for use on non-shielded portable power cables and cords. These splices are designed to be used on single or multiple conductor cables, depending on the voltage rating.			
	The 82-F1 and 82-F2 inline splices will accommodate a single-conductor cable rated up to 5 kV or single and multiple conductor cables and cords rated up to 1000 Volts (600/2000 Volts mine portable cable rating). The combined cable diameter range for these two is $0.25 - 1.2$ inches (6 – 30 mm), with a maximum single conductor size of 4/0 AWG.			
	The 82-BF1 tap splice can accommodate cables and cords rated up to 1000 Volts (600/2000 Volts mine portable cable rating) ranging in diameter from $0.25 - 0.8$ inches (6 - 20 mm) with a maximum single conductor size of 1/0 AWG.			
	These splice kits are based on 3M <sup>™</sup> Scotchcast <sup>™</sup> Flame-Retardant Compound 2131 for toughness, flexibility, environmental protection and flame retardancy. The completed splices carry Mine Safety and Health Administration Acceptance 07-KA060002-MSHA when installed in accordance with the included instructions.			
Kit Contents	Each kit contains the following materials as appropriate to make one splice or cable repair (connectors are not included due to kit range and conductor size specificity):			
	<ul> <li>One-piece removable mold</li> <li>3M<sup>™</sup> Scotchcast<sup>™</sup> Flame-Retardant Compound 2131</li> <li>Scotch® Rubber Splicing Tape 23, for sealing mold ends</li> <li>3M<sup>™</sup> Three-M-Ite<sup>™</sup> Elek-Tro-Cut<sup>™</sup> Abrasive Cloth 80J Grit</li> <li>Instructions showing proper installation techniques for splicing non-shielded portable power cables and cords</li> </ul>			
Features	<ul> <li>MSHA Accepted – carries Mine Safety and Health Administration acceptance 07- KA060002-MSHA</li> </ul>			
	<ul> <li>3M<sup>™</sup> Scotchcast<sup>™</sup> Flame-Retardant Compound 2131 – self-curing resin bonds to itself and most modern cable jackets, and requires no torch or other external heat source; forms a splice or repair that is abrasion resistant and flame retardant</li> </ul>			
	<ul> <li>Semi-flexible compound – allows "permanent" splice to bend with cable; for installation, handling, reeling, etc.</li> </ul>			
	Smooth tapered splice profile – eliminates cable bang-ups and splice end-lifting			

# 3M<sup>TM</sup> Scotchcast<sup>TM</sup> Flexible Power Cable Splicing Kits 82-F and 82-BF

## Applications 3M<sup>™</sup> Scotchcast<sup>™</sup> Flexible Power Cable Splicing Kits 82-F and 82-BF Series may be

- used to splice or re-jacket non-shielded portable power cable and portable cords:
  - For inline single-conductor cables rated up to 5 kV
  - For tap single-conductor cables rated up to 1 kV
  - For inline and tap multi-conductor cables rated up to 1 kV
  - For mine portable cable rated 600/2000 Volts (07-KA060002-MSHA)
  - For use with compression inline connectors (82-F) and compression "C" tap connectors (82-BF)

#### Sizing A. Sp

#### A. Splice Selection Table

Kit Number	Cable O.D. Range Inches(mm)	Connector Type	Number of Conductors	Connection Max. O.D. Inches(mm)	Voltage Rating (Maximum)	Conductor Size Range (AWG)
82-F1	0.25-0.80 (6-20)	Compression Inline	1	0.62 (16) Connector	5000	6-1/0
			Multi	0.90 (23) Connector Bundle	1000*	**
82-F2	0.80-1.20 (20-30)	Compression Inline	1	0.82 (21) Connector	5000	2/0-4/0
			Multi	1.30 (33) Connector Bundle	1000*	**
82-BF1	0.25-0.80 (6-20)	Compression "C" Tap	1		1000*	up to 1/0
			Multi		1000*	**

\*Mine portable cable rating of 600/2000 Volts.

\*\*Base multi-conductor selection on cable O.D. range.

#### **B.** Typical Dimensions





Kit Number	Dimensions Inches (mm)				
	L*	D	Н	W	
82-F1	8.0 (203)	1.1 (29)			
82-F2	11.5 (292)	1.6 (40)			
82-BF1	8.3 (211)		2.2 (56)	1.1 (28)	

\* "L" based on length of untrimmed mold. Trimming of mold ends to fit cable diameter reduces this dimension accordingly.

# 3M<sup>TM</sup> Scotchcast<sup>TM</sup> Flexible Power Cable Splicing Kits 82-F and 82-BF

**Installation** 3M<sup>™</sup> Scotchcast Flexible Power Cable Splicing Kits 82-F and 82-BF are designed for use with compression inline connectors (82-F) and compression "C" tap connectors (82-BF).

#### Typical De-Mold/Cure Time:

To test for cure, the compound in the splice mold funnels is checked for tack. When the compound is no longer tacky, the splice is considered ready to de-mold. Full strength and bond are attained after the resin has fully cured. Cure and de-mold time may vary, depending on ambient conditions. Some approximate times are indicated in the table below.

Ambient Temperature	Approximate De-Mold Time	Approximate Cure Time
70°F (21°C)	1.5 – 2 hrs	16 – 24 hrs
50°F (10°C)	3.5 – 4 hrs	24 – 30 hrs
32°F (0°C)	6 – 8 hrs	36+ hrs
Below 32°F (0°C)	Not recommended	

**NOTE:** Values are typical, not to be considered minimum or maximum. Always confirm that material is no longer tacky prior to de-molding.

EHS

### ▲ CAUTION

Working around energized electrical systems may cause serious injury or death. Installation should be performed by personnel familiar with good safety practice in handling electrical equipment. De-energize and ground all electrical systems before installing product.

Read all Health Hazard, Precautionary and First Aid statements found in the Material Safety Data Sheet (MSDS) and/or product label prior to handling or use.

Shelf Life & Storage	This product has a 3-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).	
Availability	Pease contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1.800.245.3573.	
Important Notice	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.	
Warranty; Limited Remedy; Limited Liability	This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.	

3M, Scotchcast, Scotch, Three-M-Ite, and Elek-Tro-Cut are trademarks of 3M Company.



Electrical Markets Division 6801 River Place Blvd. Austin, TX 78726-9000 800.245.3573 FAX: 800.245.0329 www.3M.com/electrical

Please recycle © 3M 2012 All rights reserved 78-8141-5199-5 A

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

<u>3M:</u> <u>82-F2</u> <u>82-F1</u> <u>7100010200</u>