



Article Information Sheet

Copyright, 2021, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

This Article Information Sheet is provided as a courtesy in response to a customer request. A Safety Data Sheet (SDS) has not been prepared for these product(s) because they are articles. Articles are not subject to the Occupational Safety and Health Administration's Hazard Communication Standard (29 CFR 1910.1200(b)(6)(v)). As defined in this standard: "Article" means a manufactured item other than a fluid or particle: (i) which is formed to a specific shape or design during manufacture; (ii) which has end use function(s) dependent in whole or in part upon its shape or design during end use; and (iii) which under normal conditions of use does not release more than very small quantities, e.g., minute or trace amounts of a hazardous chemical, and does not pose a physical hazard or health risk to employees.

Document Group: 05-9595-9

Issue Date: 04/30/21

Version Number: 1.04

Supersedes Date: 02/01/18

SECTION 1: Identification

1.1. Product identifier

3M™ ELECTRICAL MOISTURE BLOCK (EMB)

Product Identification Numbers

80-6104-5623-0, 80-6105-6745-7, 80-6108-4324-7, 80-6108-6647-9, 80-6109-1256-2, 80-6109-1850-2
7000058073, 7100164490

1.2. Recommended use and restrictions on use

Recommended use

Electrical, electrical moisture sealant

1.3. Supplier's details

MANUFACTURER: 3M

DIVISION: Electrical Markets Division

International Operations

ADDRESS: 3M Center, St. Paul, MN 55144-1000, USA

Telephone: 1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

This product is exempt from hazard classification according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
------------	------------	---------

ALUMINA TRIHYDRATE	21645-51-2	35 - 50
POLYBUTYLENE	9003-29-6	5 - 20
DISTILLATES (PETROLEUM), C3-6, PIPERYLENE-RICH, POLYMERS WITH ISOBUTYLENE	152698-66-3	5 - 15
LIMESTONE	1317-65-3	1 - 10
MAGNESIUM CARBONATE	546-93-0	5 - 10
Polyisobutylene	9003-27-4	1 - 10
BIS(2-ETHYLHEXYL) TETRABROMOPHTHALATE	26040-51-7	< 5
ETHYLENE-PROPYLENE-ETHYLIDENENORBORNENE TERPOLYMER	25038-36-2	< 5
ISOBUTYLENE-ISOPRENE POLYMER	9010-85-9	< 5
OXIDIZED PETROLEUM ASPHALT	64742-93-4	< 5
ANTIMONY PENTAOXIDE	1314-60-9	< 1
CALCIUM CARBONATE	471-34-1	< 1
CARBON BLACK	1333-86-4	< 1
POLYOXYETHYLENE TALLOW AMINE	61791-26-2	< 0.1

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

No need for first aid is anticipated.

Skin Contact:

No need for first aid is anticipated.

Eye Contact:

No need for first aid is anticipated.

If Swallowed:

No need for first aid is anticipated.

SECTION 5: Fire-fighting measures

In case of fire: Use a carbon dioxide or dry chemical extinguisher to extinguish.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Not applicable.

6.2. Environmental precautions

Not applicable.

6.3. Methods and material for containment and cleaning up

Not applicable.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

SECTION 8: Exposure controls/personal protection

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions. No engineering controls or personal protective equipment (PPE) are necessary.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties****Appearance****Physical state**

Solid

Color

Black

Specific Physical Form:

MITS data: ROLLS OR PADS OR STRIPS

Odor

Rubber

pH*Not Applicable***Melting point***No Data Available***Boiling Point***Not Applicable***Flash Point***Not Applicable***Flammability (solid, gas)**

Not Classified

Flammable Limits(LEL)*Not Applicable***Flammable Limits(UEL)***Not Applicable***Specific Gravity**

Approximately 1.5 [Ref Std: WATER=1]

Solubility in Water

Nil

Solubility- non-water*Not Applicable***Autoignition temperature***No Data Available***Decomposition temperature***Not Applicable***SECTION 10: Stability and reactivity**

This material is considered to be non reactive under normal use conditions.

SECTION 11: Toxicological information**Inhalation:**

No health effects are expected

Skin Contact:

No health effects are expected

Eye Contact:

No health effects are expected

Ingestion:

No health effects are expected

Additional Information:

This product, when used under reasonable conditions and in accordance with the directions for use, should not present a health hazard. However, use or processing of the product in a manner not in accordance with the product's directions for use may affect the performance of the product and may present potential health and safety hazards.

SECTION 12: Ecological information

This article is expected to present a low environmental risk either because use and disposal are unlikely to result in a significant release of components to the environment or because those components that may be released are expected to have insignificant environmental impact.

SECTION 13: Disposal considerations

Dispose of contents/container in accordance with the local/regional/national/international regulations.

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information**Chemical Inventories**

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory requirements.

SECTION 16: Other information**NFPA Hazard Classification**

Health: 1 **Flammability:** 1 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 1 **Flammability:** 1 **Physical Hazard:** 0 **Personal Protection:** A

Hazardous Material Identification System (HMIS® IV) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® IV ratings are to be used with a fully implemented HMIS® IV program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group:	05-9595-9	Version Number:	1.04
Issue Date:	04/30/21	Supersedes Date:	02/01/18

DISCLAIMER: The information in this Article Information Sheet (AIS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the AIS available

directly from 3M

3M USA AISs are available at www.3M.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[EMB-45R](#) [EMB-60R](#)