

3M™ Polyimide Film Tape 5413

Product Description

3M™ Polyimide Film Tape 5413 with DuPont™ Kapton® polyimide film and silicone adhesive used for PCB solder masking and other high temperature applications. This product is amber colored and 2.7 mil (69 microns) thick.

Key Features

- The DuPont™ Kapton® polyimide film does not soften at elevated temperatures, thus the film provides an excellent release surface at elevated temperatures
- Is dimensionally stable at high temperatures, which helps reduce rework, helping to enable high productivity
- Is flame retardant, chemical and radiation resistant which helps protect surfaces to help reduce replacement costs
- The silicone adhesive's high temperature performance helps reduce adhesive transfer which helps to eliminate cleaning, enabling high productivity
- Polyethylene tape core instead of cardboard

Product Construction/Material Description

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

3M™ Polyimide Film Tape 5413	
Property	Value
Backing	Dupont™ Kapton® Polyimide Film
Adhesive	Silicone
Color	Amber
Standard Roll Length	33 m (36yd)

Applications

- Mask for protection of gold fingers of printed circuit boards during wave solder or solder dip process.
- Release surface in fabrication of parts cured at elevated temperatures.

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Final product specifications and testing methods will be outlined in the products Certificate of Analysis (COA) that is shipped with the commercialized product.

3M™ Polyimide Film Tape 5413		
Property	Method*	Value
Adhesion to Steel:	D-3330	22 oz/in width (24 N/100 mm)
Tensile Strength at Break:	D-3579	33 lb/in width (578 N/100 mm)
Elongation at Break:	D-3579	62%
Backing Thickness:	D-3652	1.0 mil (0.03 mm)
Total Tape Thickness:	D-3652	2.7 mil (0.07 mm)
Temperature Use Range:	-	-73° to 260°C (-100° to 500°F)

3M™ Polyimide Film Tape 5413

Dielectric Strength:	D-149	7000 volts
Outgassing:	-	%TLM = 1.50, %CVCM = 0.50
Flame Retardancy:	Per UL-510 product category: OARC2 File E124809	Pass

*Methods listed as ASTM are tested in accordance with the ASTM method noted

Storage and Shelf Life

The shelf life of 3M™ Polyimide Film Tape 5413 is 36 months from the date of manufacture when stored in original cartons at 21°C (70°F) and 50% relative humidity.

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is manufactured and deemed commercially available from 3M. The COA contains the 3M test methods, specifications limits and test results for the product's performance attributes that the product will be supplied against. Contact your local 3M representative for this product's COA.

3M™ Polyimide Film Tape 5413

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE.** If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Materials Solutions Division
3M Center, Building 224-3N-11
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle.
©3M 2021. All rights reserved.
70-0703-2532-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000028910](#) [7100135111](#)