

SPEC# \_\_\_\_\_

QUANTITY \_\_\_\_\_

application:

MULTI-PURPOSE

models:

CFS11, CFS01, CFS12 & CFS02

The 3M™ Water Filtration Products line of drop-in filter housings accommodates our line of premium performance sediment and chlorine taste and odor reduction cartridges. Housings with filters can be used as in-line protection for point-of-entry, or equipment protection at point-of-use. Optional variants such as built-in valve-in-head, and opaque or transparent housings are suitable for use with most applications and budgets.

PRODUCT BENEFITS

- Various style head configurations, such as built-in pressure relief button and built-in shut-off valve, offer maximum flexibility.
- 3/4" NPT connections with 1/2" adapters provide multiple sizes for either point-of-entry or single applications with higher flow rates.
- High impact plastic designed available with either opaque or transparent housing configurations offer reliable product durability.

PRODUCT SPECIFICATIONS - Housings for 9-3/4" Cartridges

Model Number	Part Number	Description	Cartridge Replacement
CFS11S	55588-03	Opaque, Non-Valved Head	CFS8504-A, CFS117, CFS117-S, CFS110, CFS111, CFS124, CFSMZ9.75
CFS11T	55588-02	Transparent, Non-Valved Head	
CFS01S	55575-03	Opaque, Valve-In-Head	
CFS01T	55575-06	Transparent, Valve-In-Head	

PRODUCT SPECIFICATIONS - Housings for 19-1/2" Cartridges

Model Number	Part Number	Description	Cartridge Replacement
CFS12T	55589-02	Transparent, Non-Valved Head	CFS8504-B, CFS117 (2), CFS117-S (2), CFS110 (2), CFS111 (2), CFS124 (2), CFSMZ19.5, CFSFR-5, CFSFR-10
CFS02S	55576-09	Opaque, Valve-In-Head	
CFS02T	55576-10	Transparent, Valve-In-Head	




# CFS11, CFS01, CFS12 & CFS02

# 3M™ Water Filtration Products

SPEC# \_\_\_\_\_  
 QUANTITY \_\_\_\_\_  
 MODEL NUMBER \_\_\_\_\_  
 PART NUMBER \_\_\_\_\_

## PHYSICAL SPECIFICATIONS

- System maximum operating pressure of 125 psi (862 kPa) and operating temperatures of 100°F (37.8°C).



**⚠ WARNING: To reduce the risk associated with the ingestion of contaminants:**

- Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.

CUNO Incorporated recommends regularly scheduled maintenance and replacement of the filter cartridge(s) in order for the product to perform as advertised/sold. CUNO shall not be liable for system failures due to improper maintenance.

## LIMITED WARRANTY

CUNO Incorporated warrants this Product (excluding disposable filter cartridge(s)) to be free from defects in material and workmanship for five (5) years from the date of purchase. The disposable filter cartridge is warranted from defects in material and workmanship for a period of one (1) year from the date of purchase. This warranty does not cover failures resulting from abuse, misuse, alteration or damage not caused by CUNO or failure to follow installation and use instructions. If the Product is defective CUNO will replace the Product or refund your Product purchase price. CUNO will not be liable for any indirect, special, incidental, or consequential damages arising from the use of this Product. Some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation may not apply to you. To obtain warranty service, mail your request to Warranty Claims, CUNO Incorporated, 400 Research Parkway, Meriden, CT 06450. Proof of purchase (original sales receipt) must accompany the warranty claim, along with a complete description of the Product, model number and alleged defect. This warranty gives you specific legal rights and you may have other rights which vary from state to state, or country to country.

## IMPORTANT: INSTALLATION TIPS

These installation tips are for informational purposes only and are not intended to be used as actual installation instructions. **CAUTION:** To reduce the risk associated with property damage due to water leakage:

- **Read and follow** Use Instructions before installation and use of this system.
- Installation and use **MUST** comply with all state and local plumbing codes.
- **Protect from freezing**, remove filter cartridge when temperatures are expected to drop below 40°F (4.4°C).
- **Do not install on hot water supply lines.** The maximum operating water temperature of this filter system is 100°F (37.8°C).
- **Do not install** if water pressure exceeds 125 psi (862 kPa). If your water pressure exceeds 80 psi (552 kPa), you must install a pressure limiting valve. Contact a plumbing professional if you are uncertain how to check your water pressure.
- **Do not install** where water hammer conditions may occur. If water hammer conditions exist you must install a water hammer arrester. Contact a plumbing professional if you are uncertain how to check for this condition.
- The disposable filter cartridge **MUST** be replaced every 12 months, at the rated capacity or if a noticeable reduction in flow rate occurs.

**3M**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000001643](#) [7000125376](#)