

3M™ Protective Coverall 4515

Description

The 3M™ Protective Coverall 4515 is designed to help protect against certain light liquid splashes (Type 6) and hazardous dusts (Type 5).

The key features include:

- Breathable material to help reduce heat build-up and promote comfortable wear
- Elasticized waist, ankles, and wrists for convenience and freedom of movement
- Two-way zipper with storm flap

Materials

- Suit: SMS Polypropylene, White, Red, Orange, Blue
- Zipper: Nylon on Polyester Braid
- Elastic: Neoprene Rubber
- Thread: Polyester
- Basis Weight: 50 grams/m²

This product does not contain components made from natural rubber latex.

Approvals

CE approved under PPE Directive (89/686/ECC), Category III.

Article 10 Certification: BTTG Testing & Certification Ltd. Notified Body Number: 0338. Article 11B Supervision: SGS United Kingdom, LTD.

Notified Body Number: 0120.

Comfort and Protection



Liquid Protection Type 6 (EN 13034). Whole suit reduced spray test (EN ISO 17491-4-2008)*



Dust Protection Type 5 (EN ISO 13982-1:2004). Inward Leakage results:
L_{gm,82/90} < 30 %; L_{S,8/10} < 15 %.



Nuclear Radioactive particulates (EN 1073-2:2002), Class 1***. Does not offer protection against radiation.

* In the whole suit test, liquid spray is applied to the subject for 1 minute. During this time the subject moves gently and is rotated through 360°. A total of 1.88 liters is sprayed from four nozzles. The clothing is allowed to drain for 2 minutes and then the absorbent coverall is inspected for stains which are compared to a calibration stain. Requirement: Passes when the stained area inside is smaller than 3 times the calibration stain area.

** All apparel must be suitably grounded for anti-static treatment to be effective. Electrostatic propensity may decrease with wearing time and/or severe conditions.

*** Except puncture resistance.

Applications and Performance

* For additional chemical penetration and repellency data, please contact your local 3M Technical Service Representative.

Non-Hazardous Particulates	Yes	Hazardous Liquid Splash	No*
Non-Hazardous Liquid Splash	Yes	Hazardous Liquid Spray	No
Hazardous Dusts and Fibers	Yes	Organic Solvents	No
Liquid Continuous Contact/Immersion	No	Acids/Alkalis	Yes, if chemical is compatible with suit material*
Gases and Vapors	No		

Typical Applications

Typical applications may include insulation installation, asbestos and lead abatement, coal dust in power plants, metal polishing, general powder handling, general industrial clean-up and processing, and granular fertilizer application.

In all cases a risk assessment should be carried out. Users must be trained and have read all *User Instructions*. Use limitations and performance data should be considered to ascertain the protection required. If in doubt, contact a safety professional.

Performance

The table below shows the performance of this product when tested under laboratory conditions. Please note that the tests may not reflect the reality of use and do not account for factors such as excessive heat and mechanical wear.

Test	Standard	Result	Standard*	Class**/Result
Abrasion	ASTM D4157 Cycles to Rupture	No data	EN 530	Class 1
Flex Cracking			ISO 7854	Class 2
Tear Resistance Trapezoidal	ASTM D5733 (warp direction/fill direction)	10 lbf / 18 lbf	ISO 9073-4	Class 1
Tensile Strength	ASTM D751, Section 11, Procedure A (longitude/traverse)	No data	ISO 13934-1	Class 1
Puncture Resistance	ASTM D2582 (MD/CD)	31N / 40N	EN 863	Class 1
Bursting Resistance	ASTM D751, Section 18	35 psi	ISO 13938-1	Class 1
Resistance to Ignition	CPSC 16 CFR PT 1610	Class 1	EN 13274-4	Pass
Seam Strength	ASTM D751, Section 66 (Peak Load/Seam Strength)	15 lbf / 7 lbf/in	EN ISO 13935-2	Class 3
Hydrostatic Resistance	ASTM D751, Procedure B	No data		
Repellency to Liquids*** – 30% H ₂ SO ₄			EN ISO 6530	Class 3 of 3
Liquid Penetration Resistance*** – 30% H ₂ SO ₄			EN ISO 6530	Class 3 of 3
Repellency to Liquids*** – 10% NaOH			EN ISO 6530	Class 3 of 3
Liquid Penetration Resistance*** – 10% NaOH			EN ISO 6530	Class 3 of 3
Radioactive Particulates			EN 1073-2	Class 1 of 3

* The standards EN 13034:2005 and EN ISO 13982-1:2004, and EN 1073-2:2002 define performance classes.

** The maximum Class is 6 unless otherwise noted.

*** The European Standard EN ISO 6530 measures liquid penetration through a fabric and liquid repellency by a fabric. The test simulates exposure to small amounts of chemicals (10 ml) for 1 minute duration only. The penetration index refers to the percentage of the original quantity which penetrates the fabric within 1 minute (in a detector beaker) as a percentage of the original quantity.

Use Limitations


Do not use for:

- Contact with heavy oils, sparks or flames, or combustible liquids
- Exposure situations resulting in spray or liquid buildup on the suit
- Environments with high mechanical risks (abrasions, tears, cuts)
- Environments with exposure to hazardous substances beyond CE Type 5/6 certification
- Environments with conditions of excessive heat

Sizing

An appropriate size garment should be selected to allow sufficient movement for the task. Meets ANSI 101-1996 (R2008) sizing guidelines.

	Height		Chest	
M	66 – 69 in	167 – 176 cm	36 – 39 in	92 – 100 cm
L	69 – 71 in	174 – 181 cm	39 – 43 in	100 – 108 cm
XL	70 – 74 in	179 – 187 cm	43 – 45 in	108 – 115 cm
XXL	73 – 76 in	186 – 194 cm	45 – 49 in	115 – 124 cm
3XL	76 – 78 in	194 – 200 cm	49 – 52 in	124 – 132 cm
4XL	78 – 81 in	200 – 206 cm	52 – 55 in	132 – 140 cm



Storage and Disposal

- Store in dry, clean conditions in original packaging
- Store away from direct sunlight, sources of high temperature, and solvent vapors
- Store within the temperature range -20°C to +25°C (-4°F to +68°F) and with relative humidity below 80%
- Shelf life is three years from date of manufacture when stored as stated above
- Replace garments if damaged, heavily contaminated or in accordance with local work practice
- Handle and dispose of contaminated garments with care and in accordance with national regulations



Limited Use



Do not tumble dry



Do not wash



Do not dry-clean



Do not bleach



Flammable — keep away from sparks or flames



Do not iron

Product must never be altered or modified.

For more information on 3M products and services please contact 3M.

Important Notice

This guide is only an outline. It should not be used as the only means for selecting protective apparel. Before using any protective apparel, the wearer must read and understand the user instructions for each product. Specific country legislation must be observed. If in doubt, contact a safety professional. Sections of the most appropriate PPE will depend on the particular situation and should only be made by a competent person knowledgeable of the actual working conditions and the limitations of PPE.

Final determination as to the suitability of these products for a particular situation is the user's responsibility. This information is subject to revision at any time. Always read and follow all *User Instructions* supplied with your 3M™ Protective Coveralls in order to ensure correct operation. If you have questions contact 3M Technical Service.

WARRANTY: 3M will replace or refund the purchase price of any Occupational Health and Environmental Safety Division (OH&ESD) product found to be defective in material, manufacture, or not in conformance with any express warranty. This warranty is exclusive and is in lieu of any implied warranty of merchantability or fitness for a particular purpose.

LIMITATION OF LIABILITY: Except as provided above, 3M shall not be liable or responsible for any loss or damage, whether direct, indirect, incidental, special or consequential rising out of the sale, use or misuse of 3M OH&ESD products, or the user's inability to use such products. THESE REMEDIES SET FORTH HEREIN ARE EXCLUSIVE.



Occupational Health and Environmental Safety Division

3M Center
Building 235-2NW-70
St. Paul, MN 55144-1000

3M Canada Company OH&ESD

P.O. Box 5757
London, Ontario N6A 4T1
Canada

For More Information

Technical Assistance in U.S. 1-800-243-4630
3M.com/PPESafety or m.3M.com/PPESafety
Technical Assistance in Canada 1-800-267-4414
3M.ca/PPESafety

3M is a trademark of 3M, used under license in Canada. Please recycle. Printed in USA. © 3M 2012. All rights reserved. 75-0501-0802-8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[4515-2XL-White](#) [7000089612](#) [7000089615](#) [7000089619](#) [7000089623](#) [7000089624](#)