

**3M™ Tripolarized Wiremount Socket, 820 Series  
3M™ 4-Wall, Tripolarized Header, 810 Series**

**0.050" x 0.100" (1.27mm x 2.54mm) Pitch**

**Product Specification 78-5102-0074-0**

**Released: 2-22-2022**



## 1. Scope

This document summarizes test methods, test conditions and product performance requirements for the 3M™ Tripolarized Wiremount Socket, 820 Series, 82XXX-600X-RB and 3M™ 4-Wall, Tripolarized Header, 810 Series, 81XXX-XX0X0X-RB. Listings of materials, finishes, test conditions, and test standards are included in this specification. In the event of conflict between this specification and any documents listed below, the listed documentation supersedes this specification.

## 2. 3M Documents

78-5100-0254-2 TS-0254, Technical Data Sheet for 3M™ Tripolarized Wiremount Socket, 820 Series

78-5100-0253-4 TS-0253, Technical Data Sheet for 3M™ 4-Wall, Tripolarized Header, 810 Series

34-7028-4354-0 3443-113 3M™ Locator Plate Instructions

## 3. Performance and Test Description

Unless otherwise specified, all tests shall be performed on 82100 sockets mated to 81100 headers using 3447/100, 3609/100, 3754/100, and 3756/100 cable at ambient environmental conditions per EIA-364. Unless otherwise specified, all values and limits are typical of those obtained by qualification testing of the subject product. All specifications are subject to revision and change without notice from 3M.

## 4. Requirements Overview

### 4.1 Ratings

Dielectric withstanding voltage: 500 VAC<sub>RMS</sub> at sea level

Current: ( EIA-364-070A method 2, 30°C maximum temperature rise. )

0.75 Amperes, all contacts powered

2.00 Amperes, 4 contacts powered

3.00 Amperes, 1 contact powered

UL: 0.75A, 30V, 125°C

CUL: 0.75A, 30V, 125°C

Temperature: -55°C to +105°C

Insulation resistance: >1 x10<sup>9</sup>Ω at 500 VDC

Process Temperature (Header): 260°C

Moisture Sensitivity Level (Header): 1

### 4.2 Materials

Socket

Insulation: Glass Filled PBT

Cover Clip: Stainless Steel

Strain Relief: Stainless Steel

IDC Contact: Beryllium Copper Alloy

Header

Body Insulation: High Temperature LCP

Latch Insulation: High Temperature LCP

Pin Contact: Copper Alloy

### 4.3 Finishes

Plating: (socket and header)

Nickel: 50 - 150 μ inches, ASTM B689-97, SAE AMS-QQ-N-290

Gold - Wiping Area: 30 μ inches Average, MIL-G-45204 Type II, Grade C

Tin - Socket IDC: Matte Sn, 100 - 300 μ inches

Tin - Header Solder Tails: Matte Sn, 100 - 300 μ inches

**3M Electronic Materials Solutions Division**

**Interconnect Products**

**13011 McCallen Pass Bldg. C**

**Austin, TX 78753-5380**

**www.3Mconnectors.com**

3M™ Tripolarized Wiremount Socket, 820 Series, 3M™ 4-Wall, Tripolarized Header, 810 Series

#### 4.4 Cable Accomodation

General Accomodation:

30 AWG, 0.025" pitch, stranded or solid conductor, flat cable, PVC, TPE, FEP, PO insulation

3M™ Ribbon Cables:

3M™ Round Conductor Flat Cable, 3754 Series: PVC, round stranded conductor

3M™ Round Conductor Flat Cable, 3447 Series: PVC, round solid conductor

3M™ Round Conductor Flat Cable, 3756 Series: TPE, round stranded conductor

3M™ Round Conductor Flat Cable, 3749 Series: TPE, round solid conductor

3M™ Round Conductor Flat Cable, 3609 Series: FEP, round stranded conductor

3M™ Round Conductor Flat Cable, 3604 Series: FEP, round solid conductor

3M™ Round Conductor Flat Cable, HF447 Series: PO, Halogen Free, round solid conductor

3M™ Round Conductor Flat, Controlled Impedance Cable, 7700 Series: PO, shielded, round solid conductor

3M™ Jacketed and Shielded Ribbon Cables:

3M™ Pleated Foil Shielded Cable, 90101 Series: TPE/PVC, round solid conductor, flat jacketed

3M™ Pleated Foil Shielded Cable, 90111 Series: TPE/PVC, round solid conductor, flat jacketed

3M™ Pleated Foil Shielded Cable, 90201 Series: TPE/TPE, round solid conductor, flat jacketed

3M™ Pleated Foil Shielded Cable, 90202 Series: TPE/TPE, round stranded conductor, flat jacketed

3M™ Pleated Foil Shielded Cable, 90211 Series: TPE/TPE, round solid conductor, flat jacketed

3M™ Pleated Foil Shielded Cable, 93101 Series: TPE/PVC, round solid conductor, flat jacketed

#### 4.5 Regulatory Compliance

For regulatory information about this product, visit [3M.com/regs](http://3M.com/regs) or contact your 3M representative.

#### 5. Electrical

Description or parameter	Values & limits	Units	Requirement or conditions	Test Standard or method
Dielectric withstanding voltage	500	VAC <sub>RMS</sub>	Measured between adjacent and opposing contacts. No disruptive discharge during 1 minute duration. Sea level with 70% relative humidity.	EIA-364-20F Method A Test Cond I
Dielectric breakdown voltage	1000	VAC <sub>RMS</sub>	Ramp assembled pair at 500V/s until electrical arc. Sea level with 70% relative humidity. Excludes cable.	EIA-364-20F Method A Test Cond I
Current rating	3.00	Amperes	1 line driven. 30°C temp. rise. 20% derated.	EIA-364-70A Method 2
	2.00		4 line driven. 30°C temp. rise. 20% derated.	
	0.75		All line driven. 30°C temp. rise. 20% derated.	
Low level connection resistance	<10	Milliohms	10 milliohm maximum ΔR contact resistance per mated interface throughout testing.	EIA-364-23C
Insulation resistance	>1 x 10 <sup>9</sup>	Ohms	Measured between adjacent and opposing contacts. 500 VDC for 1 minute duration.	EIA-364-21F

3M Electronic Materials Solutions Division

Interconnect Products

13011 McCallen Pass Bldg. C

Austin, TX 78753-5380

[www.3Mconnectors.com](http://www.3Mconnectors.com)

**6. Mechanical**

Description or parameter	Values & limits	Units	Requirement or conditions	Test Standard or method
Header pin retention / contact	>500	gF	Average Force / pin required to remove pin from header body.	EIA-364-29B
Vibration	≤10	ns	Mated connectors shall exhibit no discontinuities greater than specified. 10 milliohm maximum $\Delta R$ contact resistance per mated interface throughout testing.	EIA-364-28F Condition V, Level A, 1.5hrs
Mechanical Shock	≤10	ns	Mated connectors shall exhibit no discontinuities greater than specified. 10 milliohm maximum $\Delta R$ contact resistance per mated interface throughout testing.	EIA-364-27C Table 1 Test Cond. A
Mating Force / contact	1.12 max	N	Mated to a .015" square pin. No latches. (Insertion Force)	EIA-364-13E
Unmating Force / contact	0.33 min	N	Mated to a .015" square pin. No latches. (Withdrawl Force)	EIA-364-13E
Latch Retention Force	> 130	N	Retention force of 2 latches on header, mated to socket. Straight pull on cable.	N/A
Durability (Full)	50	Mating cycles	10 milliohm maximum $\Delta R$ contact resistance per mated interface throughout testing.	EIA-364-09C

**7. Physical**

Description or parameter	Values & limits	Units	Requirement or conditions	Test standard or method
Visual	na	na	No defects such as deformation, blister, damage, crack, etc.	EIA-364-18A
Plating thickness Nickel Gold SN	50-150 30 100-300	Microinches	Average of random measurements from any 3 lots.	EIA-364-48 (A)
Header solderability, lead-free dip test	>95	Percent	Coverage of solderable area.	EIA-364-52 (A) Category 3

**8. Environmental**

Description or parameter	Values & limits	Units	Requirement or conditions	Test Standard or method
Temperature Life (Thermal Aging)	105	degrees C	1008 hours. No physical abnormalities . 10 milliohm maximum $\Delta R$ contact resistance per mated interface throughout testing.	EIA-364-17C Method A Condition 4
Humidity Temperature Cycling	10	24 hr cycles	25-65 C / 90-98%RH with one -10 degree C subcycle. 10 milliohm maximum $\Delta R$ contact resistance per mated interface throughout testing.	EIA-364-31F Method IV Fig 1
Thermal Shock	5	cycles	-55 to +105 degrees C. No evidence of mechanical damage. 10 milliohm maximum $\Delta R$ contact resistance per mated interface throughout testing.	EIA-364-32G Method A Test Cond. VII
Salt Spray	5	% NaCl	48 hours. 10 milliohm maximum $\Delta R$ contact resistance per mated interface throughout testing.	EIA-364-26C Test Cond. B
Moisture Sensitivity Level (Header)	1	MSL	260 C Reflow. No defects such as deformation, blister, damage, crack, etc., must maintain dimensional stability.	J-STD-020E




**9. Test Sequence****9.1 Sequenced Tests****TEST FLOW**

Test	Sequence Numbers for Test Group				
	A	B	C	D	E
Visual	0, 8	0,4	0,6	0,6	0,6
Low Level Connection Resistance (LLCR)	1,3,5,7	1,3	1,3,5	1,3,5	
Durability (Full)	2			2	3
Mechanical Shock			2		
Vibration			4		
Thermal Shock	4				
Humidity Temperature Cycling	6				
Temperature Life (Thermal Aging)		2			
Salt Spray				4	
Dielectric Withstand Voltage					1,4
Dielectric Breakdown Voltage					7
Insulation Resistance					2,5
Temperature Rise vs. Current					

**9.2 Independent Tests**

1. Plating Thicknesses
2. Header Solderability
3. Header Moisture Sensitivity Level
4. Header Pin Retention
8. Mating Force / Contact
9. Unmating Force / Contact
10. Latch Retention Force

**3M Electronic Materials Solutions Division****Interconnect Products****13011 McCallen Pass Bldg. C****Austin, TX 78753-5380****www.3Mconnectors.com**

**10. Figures****10.1 Current Rating****3M Electronic Materials Solutions Division****Interconnect Products****13011 McCallen Pass Bldg. C****Austin, TX 78753-5380****www.3Mconnectors.com**

## 11. Agency Listings

### 11.1 Underwriters Laboratories (UL)

Agency	File No.
UL	E68080
CUL	E68080

Unless otherwise noted, references to industry specifications are intended to indicate substantial compliance to the material elements of the specification. Such references should not be construed as a guarantee of compliance to all

Regulatory: For regulatory information about this product, visit [3M.com/regs](http://3M.com/regs)

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** If the 3M Product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M is a trademark of 3M Company.  
Please recycle.  
©3M 2022. All rights reserved.

**3M Electronic Materials Solutions Division**  
**Interconnect Products**  
**13011 McCallen Pass Bldg. C**  
**Austin, TX 78753-5380**  
**[www.3Mconnectors.com](http://www.3Mconnectors.com)**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[81040-600303](#) [81050-600403](#) [81068-660C07](#) [81080-550303](#) [81080-660C07](#) [81068-650301](#) [81080-600301](#) [81100-550303](#) [81020-650303-RB](#) [81026-650203-RB](#) [81026-650C07-RB](#) [81026-660C04-RB](#) [81036-500303-RB](#) [81036-550203-RB](#) [81036-660C04-RB](#) [81040-660201-RB](#) [81050-560203-RB](#) [81060-560203-RB](#) [81068-600303-RB](#) [81068-650C07-RB](#) [81068-660C07-RB](#) [81080-650C07-RB](#) [81080-660203-RB](#) [81100-660C07-RB](#) [81026-600203-RB](#) [81080-650C01-RB](#) [81036-650C01-RB](#) [81100-650C08-RB](#) [81100-650C08](#) [81080-650C01](#) [3858-040](#) [81020-550203-RB](#) [81026-660303-RB](#) [81020-650403-RB](#) [81026-600C01-RB](#) [81026-660C01-RB](#) [81036-500203-RB](#) [81036-560203-RB](#) [81036-660203-RB](#) [81050-660C04-RB](#) [81050-660C07-RB](#) [81050-660403-RB](#) [81060-660C07-RB](#) [81068-660203-RB](#) [3505-28](#) [81040-560203-RB](#) [81040-650203-RB](#) [81100-650C07-RB](#) [3505-29B](#) [81020-600203-RB](#) [81020-660201-RB](#) [81026-500203-RB](#) [81026-650C01](#) [81026-660C07-RB](#) [81036-600203-RB](#) [81040-500203-RB](#) [81040-600C04-RB](#) [81050-500203-RB](#) [81050-600203-RB](#) [81050-650203-RB](#) [81050-650C07-RB](#) [81050-660203-RB](#) [81068-500203-RB](#) [81068-600C01-RB](#) [81080-500203-RB](#) [81080-560203-RB](#) [81080-600203-RB](#) [81080-660403-RB](#) [81080-660C04-RB](#) [81100-600203-RB](#) [81100-660C04-RB](#) [81040-650C01-RB-WF](#) [81068-660C04-RB](#) [81040-660203-RB](#) [82020-6000-RB](#) [81026-560403-RB](#) [81080-560403-RB](#) [7000058089](#) [7010319984](#) [7010348039](#) [7010395668](#) [7010396962](#) [7100228142](#)