


3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : PS-0082
Revision : B
Revised Date : 14-Sep-2012
Issued Date : 04-Aug-2010

PRODUCT SPECIFICATION

3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36



3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : **PS-0082**
Revision : **B**
Revised Date : **14-Sep-2012**
Issued Date : **04-Aug-2010**

Table of Contents

| <u>Section</u> | <u>Content</u> | <u>Page</u> |
|----------------|---|-------------|
| | Cover page | 1 |
| | Contents | 2 |
| 1. | Scope | 3 |
| 1.1. | Content | 3 |
| 2. | Applicable Documents | 3 |
| 2.1. | Commercial Standards, Specifications and Report | 3 |
| 3. | Requirements | 3 |
| 3.1. | Design and Construction | 3 |
| 3.2. | Materials | 3 |
| 3.3. | Ratings | 4 |
| 3.4. | Performance and Test Description | 4 |
| 3.5. | Test Requirements and Procedures Summary | 5 |

3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : **PS-0082**
Revision : **B**
Revised Date : **14-Sep-2012**
Issued Date : **04-Aug-2010**

1. SCOPE

1.1. Content

This specification covers performance, tests and quality requirements for the 3M High-Routability MiniSAS Cable Assemblies, Series 8F36.

2. APPLICABLE DOCUMENTS

The following documents form a part of this specification to the extent specified herein. Unless otherwise specified, latest edition of the specification applies. In the event of conflict between requirements of this specification and product drawing, product drawing shall take precedence.

2.1. Commercial standards, specifications and report

- 2.1.1. EIA-364
- 2.1.2. SAS2
- 2.1.3. SFF-8086
- 2.1.4. SFF-8087

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of design, construction and physical dimensions specified on applicable product drawing.

3.2. Materials

- 3.2.1. Plug overmold
Material: High Temperature Thermoplastic
Flammability: UL94V-0
- 3.2.2. Paddlecard
Material: FR4
Mating pad underplating: Min 100u" Ni
Mating pad finish: Min 30u" Au
- 3.2.3. High-speed Ribbon Twin Ax Cable
See related specification PS-0079 for ribbon twin ax cable material information

3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : PS-0082
Revision : B
Revised Date : 14-Sep-2012
Issued Date : 04-Aug-2010

3.3. Ratings

- 3.3.1. Current rating: 0.5 A/contact
- 3.3.2. Operating temperature: -20 to +80 deg C

3.4. Performance and Test Description

Product is designed to meet electrical, mechanical and environmental performance requirements specified in section 3.5. All tests are performed at ambient environmental conditions per EIA-364 unless otherwise specified.

The mated boardmount connector used in these tests was the 3M MiniSAS internal right-angle connector, series 8AB36 (found on tech sheet TS-2208).

3.5. Test Requirements and Procedures Summary

| Test Description | Test Condition | Requirement |
|--------------------------------------|---|--|
| ELECTRICAL | | |
| Withstanding voltage | 300 V DC applied for 1 minute between adjacent signal wires, between signal wire and shield, and between sideband and shield per EIA-364-20 | No breakdown; Current leakage < 1 mA |
| Insulation resistance | 100V applied for 1 minute between adjacent signal wires, between signal wire and shield, and between sideband and shield per EIA-364-21 | >100 Megohms |
| Low level contact Resistance (LLCR). | EIA-364-23 Subject mated contacts assembled and in housing to 20 mV maximum open circuit at 100Ma maximum. | Initially 80mΩ maximum. Resistance increase 20mΩ maximum after stress per mated connector system. Connector with 25mm cable length. |

3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : **PS-0082**
Revision : **B**
Revised Date : **14-Sep-2012**
Issued Date : **04-Aug-2010**

SIGNAL INTEGRITY

| | | |
|---|---|---|
| Impedance, mated cable assembly | Risetime of 70 ps (20/80%) | 100 +/- 10 ohms |
| Differential insertion loss, SDD21 | 1 meter assembly measured over frequency range 50 MHz to 4.5 GHz | Meets SAS2 limit line: -6dB up to 4.5 GHz |
| Differential reflection loss, SDD22 | Half and one meter assemblies measured from 50 MHz to 6 GHz | Meets SAS2 limit line: < -10 dB up to 2.075 GHz < $-7.9 + 13.3 \times \log(f / 3 \text{ GHz})$ between 2.075 and 6 GHz |
| Differential-to-common mode conversion, SCD21 | Half and one meter assemblies measured from 50 MHz to 6 GHz | Meets SAS2.1 limit line: < -18 dB up to 6 GHz |
| Differential to common mode reflection, SCD22 | Half and one meter assemblies measured from 50 MHz to 6 GHz | Meets SAS2 limit line: < -26 dB up to 300 MHz < $-12.7 + 13.3 \times \log(f / 3 \text{ GHz})$ between 300 MHz and 6 GHz < -10 dB between 4.8 and 6 GHz |
| Near End Crosstalk | Half and one meter assemblies measured from 50 MHz to 6 GHz . Total NEXT calculated as described in table 52 of SAS2 standard (rev 16) | Meets SAS2 limit line: < -26 dB up to 6 GHz |

3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : PS-0082
Revision : B
Revised Date : 14-Sep-2012
Issued Date : 04-Aug-2010

MECHANICAL

| Critical Dimension Measurement | Measure dimensions specified in applicable product drawing. | Product shall meet requirements of applicable product drawing. |
|--------------------------------|---|--|
| Durability | 250 cycles Measured according to EIA-364-09 | Maximum initial R of 80 milliohms and maximum delta R of 20 milliohms. Connector with 25mm cable length. |
| Mechanical Shock | Mated connectors tested according to EIA-364-27, Test Condition "H". Normal duration 11 ms, 30g peak acceleration, ½ sine wave, 3 times each in +/- X, Y, & Z (18 shocks total) | No physical abnormalities after test. No electrical discontinuity > 1 us. Maximum initial R of 80 milliohms and maximum delta R of 20 milliohms Connector with 25mm cable length. |
| Random Vibration | Mated connectors tested according to EIA-364-28, Test Condition VII, letter D. Frequency 20 – 500 Hz, 3.10 g RMS, 15 min duration | Maximum initial R of 80 milliohms and maximum delta R of 20 milliohms Connector with 25mm cable length. |
| Removal Force | Measured according to EIA-364-13 | 49 N Maximum. |
| Insertion Force | Measured according to EIA-364-13 | 55.5 N Maximum. |

3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : **PS-0082**
Revision : **B**
Revised Date : **14-Sep-2012**
Issued Date : **04-Aug-2010**

ENVIRONMENTAL

| | | |
|---------------|---|--|
| Aging (flat) | 70°C for 500 hours per EIA-364-17 method II, test condition A | No visual changes and Maximum initial R of 80 milliohms and maximum delta R of 20 milliohms. Connector with 25mm cable length. |
| Humidity | 10 cycles (10 days) between 25°C and 65°C at 80% to 100% RH, per EIA-364-31, table 1, test condition B, method III, figure 1. No bias and no sub-cycle. | No visual changes and meets signal integrity specifications (impedance, s- parameters). Cable assembly |
| Thermal shock | -55°C to +85°C, 10 cycles, 1/2 hour at each temperature extreme, per EIA-364-32, Table 2, Test Condition I | No visual changes and meets signal integrity specifications (impedance, s- parameters). Cable assembly |

3M™ High Routability Internal MiniSAS Cable Assembly, Series 8F36

Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726
<http://www.3Mconnector.com>

Document No. : **PS-0082**
Revision : **B**
Revised Date : **14-Sep-2012**
Issued Date : **04-Aug-2010**

"RoHS Compliant 2002/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2005/618/EC, unless the substance is in an application that is exempt under EU RoHS. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 90 days from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[8F36-AAC105-0.50](#) [8F36-AAA105-0.50](#) [8F36-AAA105-1.00](#) [7010501874](#) [7010506995](#) [7010507141](#) [7100183372](#)
[7100183470](#)