



IL-IM-01

In-Line Filtration System for
Refrigerators/Ice Makers



Reduces:

Chlorine Taste & Odor

Spec #

Quantity

At a Glance:

- Premium performance Progressive Porosity filtration
- Standard 1/4" push-in inlet/outlet connections
- 125 psi maximum pressure rating
- 100°F (37.8) maximum operating temperature

Product Benefits:

- Reduces Chlorine Taste & Odor
- Rated for 2,500 gallons of filtration at 0.5 gpm
- 5 micron nominal filtration
- Used in appliances with ice and water dispensers
- Can also be used for drinking fountains, coffee machines and drink dispensers

Product Specifications:

Model No. (Part No.)	Service Flow Rate	Service Life	Max. Water Pressure	Max. Water Temp.	Std. Replacement Ctg. No.
IL-IM-01 (5617202)	0.5 gpm (1.9 lpm)	2,500 gallon (9,464 liters)	125 psi (862 kPa)	100°F (37.8°C)	IL-IM-01 (5617202)

IL-IM-01

In-Line Filtration System for Refrigerators/Ice Makers

Spec #


Quantity

Model Number

Part Number

Product Specifications:

- 1/4" Push-in fittings
- System is a single vessel design
- System has a maximum operating pressure of 125 psi (862 kPa) and operating temperature of 100°F (37.8°C)
- System includes 1/4" push-in fittings
- System to be installed on refrigerator/ice maker cold water line



IL-IM-01

General Product Guidelines:

⚠ WARNING: Read entire manual. Failure to follow all guides and rules could cause personal injury or property damage.

- Check with your local public works department for plumbing codes. You must follow their guidelines as you install the Water Filtration system.
- Your Water Filtration system will withstand up to 125 pounds per square inch (psi) water pressure. If your house water supply pressure is higher than 80 psi, install a pressure reducing valve before installing the Water Filtration system.

To reduce the risk associated with the ingestion of contaminants:


- DO NOT use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.

NOTICE: To reduce the risk associated with property damage due to water leakage or flooding:

- Read and follow Use Instructions before installation and use of this system.
- Change the disposable filter cartridge at the recommended interval; the disposable filter cartridge MUST be replaced every 6 months or sooner.
- Failure to replace the disposable filter cartridge at recommended intervals may lead to reduced filter performance and failure of the filter, causing property damage from water leakage or flooding.

3M Purification Inc. recommends regularly scheduled maintenance and replacement of the filters in order for the product to perform as advertised. 3M Purification Inc. shall not be liable for system failures due to improper maintenance.

Diagram shown is for reference purposes only. Read installation and operation manual prior to installing the unit.



Limited Warranty:

3M warrants this product will be free from defects in material and manufacture for one (1) year from the date of purchase. This warranty does not cover failures resulting from abuse, misuse, alteration or damage not caused by 3M or failure to follow installation and use instructions. No warranty is given as to the service life of any filter cartridge or membrane as it will vary with local water conditions and water consumption. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOMER OR USAGE OF TRADE. If the Product fails to satisfy this Limited Warranty during the warranty period, 3M will replace the Product or refund your Product purchase price. This warranty does not cover labor. The remedy stated in this paragraph is Customer's sole remedy and 3M's exclusive obligation. **For additional information, see the entire Limited Warranty located in the product Installation and Operating Instruction Manual.**

Limitation of Liability: 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states and countries do not allow the exclusion of limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.

3M Purification Inc.
400 Research Parkway
Meriden, CT 06450 U.S.A.
Toll Free: 1.800.222.7880
Worldwide: 203.237.5541
Fax: 203.238.8701
www.aquapure.com
www.3mpurification.com

3M and Aqua-Pure are trademarks of 3M Company.
NSF is a trademark of NSF International.
© 2018 3M Company. All rights reserved.
70030304205 REV 0618f



Visit www.nsf.org for the claims associated with products that are NSF listed.

Distributed by:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000050772](#)