

3M™ Scotchcast™ Electrical Resin 262

One-Part, Class B, General Purpose Epoxy Powder Resin

Product Description

3M™ Scotchcast™ Electrical Resin 262 is a widely used, well-known general purpose epoxy powder resin. A one-part, red pigmented, rapid heat-curing product, it is designed to provide a continuous, tough moisture and chemical resistant dielectric coating to a variety of substrates.

- Fast curing
- Excellent electrical properties
- Excellent thermal shock and impact resistance
- Excellent heat, chemical and moisture resistance
- Good cut-through resistance
- Excellent flow

Scotchcast Electrical resin 262 is manufactured by a fusion blend process, insuring that each individual particle of powder contains all the components necessary to effect a complete cure and attain stated performance properties.

Scotchcast electrical resin 262 is applied to an object that has been heated to a temperature above the melting point of the resin. On contact with the preheated application surface, the resin melts, flows to a controlled extent, then cures, bonding to the substrate and coalescing into a smooth, continuous, essentially uniform, thick coating. It effectively coats flat surfaces and corners, as well as, high points. Uses for Scotchcast 262 include moisture proofing and insulating armatures, stators, buss bars and toroid cores.

Scotchcast™ Electrical Resin 262 – Typical Properties

Property	Value
Color	Red
Specific Gravity ¹ (cured)	1.34
Dielectric Strength ³ 12 to 15 mil coating	1000 v/mil
Thermal Shock ² 10 cycles-75°C to 155°C 12 -15 mil coating 1/8" sandblasted steel	Passes
Impact Resistance ² 12-15 mil coating 1/8" sandblasted steel panel Gardner 5/8" Radius Impact Tester	100 inch-lbs
Cut-Through Resistance ² – 1lb wt: 1/8 AWG wire	130°C (266° F)
Edge Coverage ² 12-15 mil coating on flat	38-48%
Gel time ² @ 193°C hot plate	12-16 seconds

*Not recommended for specification purposes. Product specifications will be provided upon request.

Test Methods

¹ ASTM D-792

² 3M Test Method

³ ASTM D-149



Usage Information

Method of Application

The rapid cure of 3M™ Scotchcast™ Electrical Resin 262 permits the use of highspeed production methods. The powder can be readily applied by spraying techniques as well as through the use of fluid bed dipping of preheated parts. Automated and manual types of application equipment are both available. Equipment manufacturers' names can be suggested upon request.

Curing

The cure of Scotchcast 262 to a thermoset condition involves a time-temperature relationship. The retained heat in application units having high heat capacity is sufficient in many cases to effect a cure of the resin without the need for post-curing facilities. For example, if an application surface can retain a temperature of 204° C (400° F) for 60 seconds after coating, it will be fully cured. Small articles, or those with a large surface-to-mass ratio, lose heat rapidly and may require a higher preheat temperature and/or additional oven-curing.

The figures below represent nominal guidelines for obtaining the resin's adhesion, impact and chemical resistance characteristics.

Cure Temperature	Time
149° C (300° F)	40 minutes
177° C (350° F)	20 minutes
204° C (400° F)	60 seconds
232° C (450° F)	30 seconds

The user must determine the time required for the coated substrate to reach listed temperatures.

Handling and Safety Precautions

Read all Health Hazard, Precautionary and First Aid, Material Safety Data Sheet, and/or product label prior to handling or use.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



Corrosion Protection Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
www.3M.com/corrosion

Please recycle. Printed in USA.
© 3M 2010. All rights reserved.
80-6111-0945-7 Rev A

Preheat Temperature Range

Prior to applying Scotchcast electrical resin 262, the part must be preheated to a temperature ranging from 150° C (302° F) to 260° C (500° F). The optimum preheat temperature depends upon the size, heat capacity and configuration of the object to be coated, as well as the method of application. The ideal coating temperature will vary for each application and is best determined by experimentation.

Storage

Laboratory evaluation indicates that the usable shelf life of the product is twenty four (24) months from the date of manufacture when stored at temperatures not exceeding 27° C (80° F), providing the material is stored in its original container. Care should be taken when removing the resin from the original container to prevent inclusion of foreign material. After the resin removal, the bag should be retied immediately. This will help to avoid agglomeration caused by excess moisture. For best results, store in a cool, dry place.

Ordering Information/Customer Service

For ordering technical or product information, or a copy of the Material Safety Data Sheet, call:

Phone: 800/722-6721 or 512/984-9393

Fax: 877/601-1305 or 512/984-6296

Warranty; Limited Remedy; Limited Liability.

Because conditions of product use are outside of our control and vary widely, the following is made in lieu of all express or implied warranties: this product will conform to 3M's published product specifications and be free from defects in material and manufacture on the date of your purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective upon your receipt, your exclusive remedy shall be, at 3M's option, to replace the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:
7000057526