# 3M<sup>™</sup> Round, Shielded/Jacketed, Flat Cable

.050" 28 AWG Stranded, Mass Terminatable, PVC/PVC

3659 Series



- Round construction permits easier routing
- 28 AWG wire on .050 inch pitch permits mass termination to broad line of IDC connectors
- Continuous split/bond repeat allows for mass termination on 2.4 inch centers (approximate)
- Primary cable is zippable for branching or discrete terminations
- Meets external wiring requirements of National Electrical Code, Article 725 (CL2)
- UL listed for USA and Canadian markets
- Dual shielding provides 35 db average shielding effectiveness
- See Regulatory Information Appendix (RIA) for chemical compliance information (RIA E1 & C1 apply)

Date Modified: May 11, 2009

TS-0083-B Sheet 1 of 2

#### **Physical**

Jacket Material: Polyvinyl Chloride (PVC)

Color: Black

Primary Material: PVC

Color: Gray

Marking Standard: (UL) CL2 75C 28 AWG or AWM 20267 3M NU

• **AWM** IIA/B 80C 300V FT1 EU < 50V

**Conductors:** 28 AWG, 7 × 36 AWG [ 7 × Ø 0.127 ] Tinned Stranded Copper

Shielding: 0.001 [ 0.03 ] Thick Aluminum/Polyester Film Foil and

90% Coverage Tinned Copper Braid

### **Electrical**

Voltage Rating: USA: N.E.C. 725, CL2 or AWM; 300V Canada: 300V EU: <50V

**Insulation Resistance:**  $> 1 \times 10^{10} \Omega/10 \text{ ft.}$  [ 3m ]

Characteristic Impedance: Unbalanced Balanced

 $62 \Omega$   $106 \Omega$ 

 Capacitance:
 27.7 pF/ft [ 90.88 pF/m ]
 15.2 pF/ft [ 49.9 pF/m ]

 Inductance:
 0.11 μH/ft [ 0.35 μH/m ]
 0.17 μH/ft [ 0.57 μd/m ]

 Propagation Delay:
 1.72 ns/ft [ 5.64 ns/m ]
 1.62 ns/ft [ 5.31 ns/m ]

**Velocity of Propagation:** 59% 62%

Note: Unbalanced is measured between ground-signal-ground conductors with shield grounded. Balanced is measured between signal conductors within a pair, with the shield floating.

#### **Environmental**

**Temperature Rating:** USA: -20° C to +105° C Canada: -20° C to +80° C

Flammability Rating: USA: VW-1 Canada: FT1

UL File No.: E118773, Power Limited Circuit Cable: CL2 (or AWM Style 20267)

# 3M<sup>™</sup> Round, Shielded/Jacketed, Flat Cable

.050" 28 AWG Stranded, Mass Terminatable, PVC/PVC

3659 Series

Number of Conductors	3M Part Number	Dimension A	Dimension B Ref (See Note 2)	Inch				
09	3659/09	0.27 [ 6.9 ]	0.40 [ 10.2 ]	[mm]				
10	3659/10	0.27 [ 6.9 ]	0.45 [ 11.4 ]	Tolerance Unless Not	ted			
14	3659/14	0.31 [ 7.9 ]	0.65 [ 16.5 ]	.0 .00	.000			
15	3659/15	0.31 [ 7.9 ]	0.70 [ 17.8 ]					
16	3659/16	0.31 [ 7.9 ]	0.75 [ 19.1 ]	111011 1.11 1.03	±.010			
20	3659/20	0.34 [ 8.6 ]	0.95 [ 24.1 ]	[] Dimensions for Referenc	e Only			
24	3659/24	0.37 [ 9.4 ]	1.15 [ 29.2 ]					
25	3659/25	0.37 [ 9.4 ]	1.20 [ 30.5 ]					
26	3659/26	0.37 [ 9.4 ]	1.25 [ 31.8 ]					
34	3659/34	0.41 [ 10.4 ]	1.65 [ 41.9 ]					
36	3659/36	0.43 [ 10.9 ]	1.75 [ 44.5 ]					
37	3659/37	0.43 [ 10.9 ]	1.80 [ 45.7 ]					
40	3659/40	0.43 [ 10.9 ]	1.95 [ 49.5 ]					
50	3659/50	0.48 [ 12.2 ]	2.45 [ 62.2 ]					
60	3659/60	0.51 [ 13.0 ]	2.95 [ 74.9 ]					
64	3659/64	0.54 [ 13.7 ]	3.15 [ 80.0 ]					
Contact 3M for availability of additional conductor counts.  2.4 Ref [61]  Bonded  1.0 Ref. [25]  Paper [Mfgr Option]  PVC Jacket  PVC Jacket  PVC Primary Insulation  28 AWG, 7 X 36 AWG [7 X Ø 0.127]  Tinged Stranged Conner Conductors								
Notes:  1. Red marking on one edge of primary cable designates wire #1.  2. Dimension B pertains to bonded area only.  Ordering Information  3659 / XX XX XX  Blank = Standard SF = Splice Free  Blank = Standard SO = Continuously Bonded Wire (No Split)								
			Number of Conduc					
Note: Available in star	ndard lengths of 100 ft or 30	00 ft rolls,	(See Table)					
please specify when o	ordering. Contact 3M for ava counts and/or custom roll le	ailability of			TS-0083-B Sheet 2 of 2			

# **Regulatory Information Appendix**

#### 3M Electronic Solutions Division/Interconnect

#### **EUROPE**

### Appendix E1: European Union RoHS

Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical & Electronic Equipment, as amended by EU Commission Decision 2005/618/EC.

#### This product is RoHS Compliant 2005/95/EC.

"RoHS Compliant 2005/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2005/618/EC, unless the substance is in an application that is exempt under EU RoHS. Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

### Appendix E2: European Union RoHS

Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical & Electronic Equipment, as amended by EU Commission Decision 2005/618/EC.

This product contains lead in the compliant pin area in excess of the maximum concentration value allowed but is compliant by exemption under EU Commission Decision 2005/747/EC.

"RoHS Compliant 2005/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2005/618/EC, unless the substance is in an application that is exempt under EU RoHS. Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

## **Appendix E3: European Union RoHS**

Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical & Electronic Equipment as amended by Commission Decision 2005/618/EC.

This product contains lead in the solder tail area in excess of the maximum concentration value allowed.

Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

## **Appendix E4: European Union RoHS**

Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical & Electronic Equipment, as amended by EU Commission Decision 2005/618/EC, as amended by EU Commission Decision 2005/717/EC, as amended by EU Court of Justice Decision 2008/C 116/04

This product contains decaBDE in the insulating material in excess of the maximum concentration allowed for finished products subject to EU RoHS that are placed on the EU market after June 30, 2008.

Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

#### **Appendix E5: European Union RoHS**

Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment, as amended by EU Commission Decision 2005/618/EC.

This product contains lead in excess of the maximum concentration value allowed but is compliant by exemption under Item 6 of the Annex to the Directive.

"RoHS Compliant 2005/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2005/618/EC, unless the substance is in an application that is exempt under EU RoHS. Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

#### **CHINA**

# Appendix C1: China RoHS



Electronic Industry Standard of the People's Republic of China, SJ/T11363-2006, Requirements for Concentration Limits for Certain Hazardous Substances in Electronic Information Products.

This symbol, per Marking for the Control of Pollution Caused by Electronic Information Products, SJ/T11364-2006, means that the product or part **does not** contain any of the following substances in excess of the following maximum concentration values in any homogeneous material: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers (excluding decaBDE); or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

# Appendix C2: China RoHS



Electronic Industry Standard of the People's Republic of China, SJ/T11363-2006, Requirements for Concentration Limits for Certain Hazardous Substances in Electronic Information Products.

This symbol, per Marking for the Control of Pollution Caused by Electronic Information Products, SJ/T11364-2006, means that the product or part **does** contain a substance, as detailed in the chart below, in excess of the following maximum concentration values in any homogeneous material: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers (excluding decaBDE); or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

The numerical reference in the symbol above should not be construed as a representation regarding the product's life or an extension of a product warranty. The product warranty is stated below. In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the product Warranty stated below.

产品中有毒有害物质或元素的名称及含量 Name and Content of Hazardous Substances or Elements

部件名称	有毒有害物质或元素(Hazardous Substances or Elements)						
(Part or Component Name)	铅(Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴联苯 (PBB)	多溴二苯醚 (PBDE)	
端子镀层(contact plating)	×	0	0	0	0	0	

〇:表示该有毒有害物质在该部件所有均质材料中的含量均在SJ/T11363-2006 标准规定的限量要求以下。(Indicates that this hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement in SJ/T11363-2006.)

<sup>×:</sup>表示该有毒有害物质至少在该部件的某一均质材料中的含量超出SJ/T11363-2006 标准规定的限量要求。(Indicates that this hazardous substance contained in at least one of the homogeneous materials used for this part is above the limit requirement in SJ/T11363-2006.)

## Appendix C3: China RoHS



Electronic Industry Standard of the People's Republic of China, SJ/T11363-2006, Requirements for Concentration Limits for Certain Hazardous Substances in Electronic Information Products.

This symbol, per Marking for the Control of Pollution Caused by Electronic Information Products, SJ/T11364-2006, means that the product or part **does** contain a substance, as detailed in the chart below, in excess of the following maximum concentration values in any homogeneous material: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers (excluding decaBDE); or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's best knowledge and belief based upon information provided by third party suppliers to 3M.

The numerical reference in the symbol above should not be construed as a representation regarding the product's life or an extension of a product warranty. The product warranty is stated below. In the event any product is proven not to conform with 3M's Regulatory Information Appendix, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the product Warranty stated below.

产品中有毒有害物质或元素的名称及含量 Name and Content of Hazardous Substances or Elements

面上有每有各物灰实儿亲的名称交音量 Name and Content of Mazardous Substances of Elements						
部件名称	有毒有害物质或元素(Hazardous Substances or Elements)					
(Part or Component Name)	铅(Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
合金(Metal alloy)	×	0	0	0	0	0

O: 表示该有毒有害物质在该部件所有均质材料中的含量均在SJ/T11363-2006 标准规定的限量要求以下。(Indicates that this hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement in SJ/T11363-2006.)

#### **Important Notice**

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

#### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



3M Electronics Solutions Division

6801 River Place Blvd. Austin, TX 78726-9000 U.S.A. 1-800-225-5373 www.3m.com/interconnects

<sup>×:</sup>表示该有毒有害物质至少在该部件的某一均质材料中的含量超出SJ/T11363-2006 标准规定的限量要求。(Indicates that this hazardous substance contained in at least one of the homogeneous materials used for this part is above the limit requirement in SJ/T11363-2006.)

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### 3M:

3659/16-300 3659/34-300 3659/37-1000 3659/40-CUT-LENGTH 3659/40-100SF 3353/34-100 3353/60-100 3353/64-100 3353/64-100 3353/50-100 3353/26-100 3659/09-100SF 3659/14-100SF 3659/24-100 3659/24-100SF 3659/24-300SF 3659/37-100SF 3659/10-300SF 3659/50-300SF 3659/64-100 3659/10-100SF 3659/15-100SF 3659/15-500 3659/25-100SF 3659/34-300SF 3659/60-100SF 3659/64-300 3659/20-100SF 3659/50-100SF 3659/15-300 3659/26-300SF 3659/16-100 3659/26-300SF 3659/09300 3659/09300SF 3659/14300SF 3659/15300 3659/36300SF 3659/16300SF 3659/16300SF 3659/24300 3659/25300SF 3659/36300SF 3659/36300SF 3659/37300 3659/37300SF 3659/40300SF 3659/40300SF 3659/50300 3659/60300SF 3659/64100SF 3659/64100SF 3659/64300SF 3659/50-CUT-LENGTH 3659/26-CUT-LENGTH 3659/25-CUT-LENGTH 3659/15-CUT-LENGTH 3659/34-CUT-LENGTH 3659/37-CUT-LENGTH 3659/34-100SF 3659/34-100 3659/37-100 3659/34-100 3659/34-100 3659/34-100 3659/37-100 3659/37-100 3659/37-100 3659/34-100 3659/3