## 3M<sup>TM</sup> Scotchcast<sup>TM</sup> Electrical Resin 281

Two-Part, Semi-Flexible, Filled, Epoxy Liquid Resin

**Data Sheet May 2014** 3M<sup>™</sup> Scotchcast<sup>™</sup> Electrical Resin 281 is characterized by high temperature **Product Description** and electrical stability, and excellent retention of flexibility, even after prolonged heat aging. It can be cured at low temperatures, but the optimum properties are obtained with the higher temperature cure schedules. This resin should be used instead of 3M Scotchcast Electrical Resin 241 where greater mechanical strength, higher tensile strength, better thermal shock ad higher thermal conductivity are required. High temperature rating (155°C – Class F) **Resin Features** Low temperature curing High thermal conductivity **Applications** Impregnation and encapsulation of coils, transformers, motors and other electrical and electronic components Handling **Properties** Mix Ratio (A, B) W/t 2.3 Vol (%) 37:63 Initial Viscosity @ 23°C (73°F) A = 320,000 cpsB – 38,000 cps Mixed = 75,000 cps Density A = 1.53 kg/l (12.77 lbs/gal) B = 1.35 kg/l (11.26 lbs/gal) $A = 202^{\circ}C (395^{\circ}F)$ Flash Point  $B = 188^{\circ}C (370^{\circ}F)$ **Gel Time** 21 min. @ 121°C **Curing Guide** 75°C (167°F) 24 hrs 95°C (203°F) 6-8 hrs 120°C (248°F) 2-3 hrs



## **Typical Properties**

Not for specifications. Values are typical, not be considered minimum or maximum. Properties measured at room temperature 73°F (23°C) unless otherwise stated.

Physical Property (*See Test Method Table)	Typical Value US units (metric)
Color	Cream
Specific Gravity (Cured)	1.43
Compressive Strength* <sup>1</sup> 10% Compression	3500 psi (245 kg/cm²)
Tensile Strength* <sup>2</sup> (1/8" x ½"'Sample)	2100 psi 147 kg/cm <sup>2</sup>
Elongation* <sup>2</sup> (% @ break)	45
Flexural Strength* <sup>3</sup> (1/2" x ½" Sample)	1250 psi 87.5 kg/cm <sup>2</sup>
Hardness (Shore D instantaneous)	65
Thermal Conductivity* <sup>4</sup> (Ca./sec/cm <sup>2</sup> / °C/cm)	12 x 10 <sup>-4</sup>
Coefficient of Linear Thermal Expansion* <sup>2</sup> (23°C to 113°C) (length/unit length/°C)	15 x 10 <sup>-5</sup>
<b>Thermal Shock*<sup>5</sup> 10 cycles -</b> 65°C to 130°C <sup>5</sup> 1/4" (6,350 mm) Olyphant Inserts	Pass
Thermal Shock* <sup>4</sup>	Pass
Moisture Absorption (% weight increase, 240 hrs. @ 96% RH) <sup>4</sup>	.32
Water Immersion (sample cured 3 hrs. @120°C) 100 hrs @ 23°C - % weight gain 500 hrs @ 70°C - % weight gain 200 hrs @ 100°C - % weight gain	0.4 6.2 8.0
Thermal Aging (2 1/4 " x 2 1/4 " x 1/8" sample, 1000 hrs @130°C)% weight lossHardness Change (Shore D)Dielectric Constant (100 hertz @23°C)Dissipation Factor (100 hertz @ 23°C)Volume Resisitivity*6 (ohm-cm @ 23°C)	.17 7 3.56 .054 >10 <sup>15</sup>
<b>Thermal Aging</b> (2 1/4 " x 2 1/4 " x 1/8" sample, 1000 hrs @155°C) % weight loss Hardness Change (Shore D) Dielectric Constant (100 hertz @23°C) Dissipation Factor (100 hertz @ 23°C) Volume Resistivity* <sup>6</sup> (ohm-cm @ 23°C) Urethane (itself)	2.2 15 4.03 .032 >10 <sup>15</sup>
<ul> <li>Inermal Aging (2 1/4 ° x 2 1/4 ° x 1/8° sample, 1000 hrs @180°C)</li> <li>% weight loss</li> <li>Hardness Change (Shore D)</li> <li>Dielectric Constant (100 hertz @23°C)</li> <li>Dissipation Factor (100 hertz @ 23°C)</li> <li>Volume Resistivity*<sup>6</sup> (ohm-cm @ 23°C)</li> </ul>	3.5 18 4.71 .041 >10 <sup>15</sup>

Electrical Property (*See Test Method Table)	Typical Value US units (metric)
Electric Strength* <sup>3</sup> 1/8" (3,175 mm) sample	350 V/mil (13,8 kV/mm)
Electric Strength* <sup>2</sup> [Volts/mil 1/8" (3,175 mm) sample]	375 (14,800 volts/mm)

\*See test method table next page

	<sup>1</sup> Fed. Std. N. 406, Method 1021	<sup>4</sup> Mil-16923
	<sup>2</sup> Fed. Std. N. 406, Method 1011	<sup>5</sup> 3M Test Method
Table	<sup>3</sup> Fed. Std. N. 406, Method 1031	<sup>6</sup> Fed. Std. No. 406, Method 4041
Mixing	Mix the separate parts before removing them from their containers. They may be warmed to 60°C (140°F) to aid mixing. Weigh the correct proportions of the separate parts to within 2% accuracy and combine them. Thoroughly blend the mixture until the color is absolutely uniform, or until a homogenous mixture is attained.	
De-aerating	Air introduced during mixing can be removed by evacuating for 5 to 15 minutes at 5 to 10 mm of mercury absolute pressure. Warming the resin to 60°C (140°F) aids air removal. The container side wall should be four times the height of liquid resin to contain the foaming that takes place under vacuum.	
Casting and Impregnating	Pour the warm resin into the preheated 100°C mold. If no mold is used, dip the preheated part into the resin. Heating the resin and mold aids impregnation. For maximum impregnation, evacuate for 5 to 15 minutes at 5 mm of mercury absolute pressure, or pour under vacuum and hold for several minutes before releasing.	
Curing	Where minimum stress and maximum shock resistance are required, the lower	
	cycle to allow the resin to reach the	e curing temperature.
Handling & Safety	Read all Health Hazard, precaution Material Safety Data Sheet (MSDS handling or use.	ary and First Aid statements found in the and/or product label of chemicals prior to
Shelf-Life & Storage	These resins have a 2 year shelf stored in a humidity controlled stored relative humidity). It is 3M's standa at least 50% of its shelf life remain life requirement may require a lar scheduled product run. Contact y Service for specific shelf life MOC accepted on special shelf life reque	life following the date of manufacture when brage (10°C/50°F to 27°C/80°F and <75% and procedure to ship any resin product with ing. Any special request for a specific shelf ger than stated MOQ that justifies a non- your 3M sale representative or Customer Q requirements. No product returns will be est orders.





Brookfield Viscosity vs. Time @ 75°C (170°F) & 95°C (200°F)

**Dielectric Constant** Fed. Std. 406, Method 4021 (Test Frequencies in Hertz)

## 3M<sup>™</sup> Scotchcast<sup>™</sup> Electrical Resin 281

**Dissipation Factor** Fed. Std. 406, Method 4021 (Test Frequencies in Hertz)



Volume Resistivity		
(OHM-CM)		
Fed. Std. 406, Method 4041		

Important Notice:	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.
Warranty; Limited Remedy; Limited Liability:	This product will be free from defects in material and manufacture at the time of purchase. <b>3M MAKES</b> <b>NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY</b> <b>OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.</b> If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. <b>Except where prohibited by law,</b> <b>3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.</b>

3M and Scotchcast are trademarks of 3M Company.



Electrical Markets Division 6801 River Place Blvd. Austin, TX 78726-9000 800.676.8381 Fax 800.828.9329 www.3M.com/OEM

Please recycle. © 3M 2014 All rights reserved. 78-8124-5686-7 Rev E

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

<u>3M</u>: 7000006257 7000057525