


# 3M™ Mini D Ribbon (MDR) Cable Assembly

.050" Twisted Pair Digital Transmission System - 26 to 26 Position

4926-01XX



- .050" MDR differential signal transmission interconnect
- Flexible twisted pair round cable with overall braid/foil shield
- Ribbon-type contact for reliable repetitive plugging/unplugging
- Quick release latches
- RoHS\* compliant

Date Modified: May 12, 2006

TS-0758-06  
Sheet 1 of 3

---

## Physical

### Connector Contact Plating

Wiping Area: Wiping Area: 30  $\mu$ " [ 0.76  $\mu$ m ] Min. Gold  
Shell Material: Acrylonitrile Butadiene Styrene (ABC)  
Cable Color: Beige  
Cable Jacket Material: Polyvinyl Chloride (PVC)  
Flammability: AWM VW-1  
Shell Color: Beige

---

## Electrical

Voltage Rating: 30 V  
Current Rating: 1 A  
Insulation Resistance:  $> 5 \times 10^8 \Omega$  at 500 Vdc  
Withstanding Voltage: 500 Vrms for 1 minute  
Twisted Pairs  
Characteristic Impedance: 100 $\Omega$   
Conductor: 28 AWG Stranded

---

## Environmental

Temperature Rating: -20°C to +75°C  
Flammability Rating: N.E.C. 725, CL2


\*RoHS = Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment  
"RoHS compliant" means that the product or part does not contain any of the following substances in excess of the following maximum concentration values in any homogeneous material, unless the substance is in an application that is exempt under RoHS: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers; or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's knowledge and belief based upon information provided by third party suppliers to 3M.

UL File No.: E86982

# 3M™ Mini D Ribbon (MDR) Cable Assembly

.050" Twisted Pair Digital Transmission System - 26 to 26 Position

4926-01XX



mm  
[Inch]

Tolerance Unless Noted		
	0.0	0.00
mm	±.1	±.10

[ ] Dimensions for  
Reference only

**MDR 26 Position Plug**  
( Both Ends )



Assembly Length Tolerance

Cable Length:  
0.5 to 1.5 meters -0 + .05 meters  
2 to 10 meters -0 +3% of length

## Ordering Information

**4926-01XX**

Length  
01 = 1 meter  
02 = 2 meter  
03 = 3 meter  
05 = 5 meter  
24 = 2 ft. (Special order)

Note: Call 3M for details on custom polarizing keys for receptacle and plugs.

TS-0758-06  
Sheet 2 of 3

**3M**

**Interconnect Solutions**

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.  
For technical, sales or ordering information call  
**800-225-5373**

# 3M™ Mini D Ribbon (MDR) Cable Assembly

.050" Twisted Pair Digital Transmission System - 26 to 26 Position

4926-01XX


## MDR 26 Position, Pinout P26-7 / F26-7, Version 3644B/26 Cable

(Note: Cable assembly is reversible)


Transmitter (Host)  
3M MDR SMT Receptacle

Cable Assembly

Receiver (Monitor)  
3M MDR SMT Receptacle



Symbols Key:

  
100 ohm balanced  
twisted pair

TS-0758-06  
Sheet 3 of 3



Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call

800-225-5373

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



### 3M Electronics

6801 River Place Blvd.  
Austin, TX 78726-9000  
800/225-5373  
[www.3M.com/electronics](http://www.3M.com/electronics)

## Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Minimum 10%  
Post-Consumer Fiber

Printed in USA.

© 3M 2006

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[4926-0101](#) [4926-0102](#) [4926-0103](#) [4926-0105](#)