

3M™ 100 Series High Performance Liquid Filter Bags

3M™ 100 Series - High Performance Liquid Filter Bags

The 3M™ 100 series high performance liquid filter bag is constructed of polypropylene melt blown microfibers, allowing for very fine particle capture at high efficiencies. All 3M 100 series liquid filter bags are over 90% efficient at their suggested application rating. The 3M filter offers an excellent balance of high efficiencies with very low initial pressure drops. The bag construction makes this filter an easy to use, convenient, high performance alternative to filter cartridges.

The 3M 100 series liquid filter bag can also adsorb unwanted trace oils that frequently occur in processed fluids. The high amount of surface area due to the polypropylene microfiber construction, results in oil holding capacities from 10-20 times the filter's own weight.

Applications

• Acids and bases	• Machine coolants
• Amines	• Makeup water
• Carbon beds	• Organic solvents
• Completion fluids	• Photo chemicals
• Deep wells	• Plating solutions
• Desalination	• RO membranes
• DI resins	• Storm Water
• Glycol	• Wastewater
• Groundwater clean-up	• Waterflood

Materials of Construction

Filter Media:

Meltblown polypropylene microfiber filter media provides high particle removal efficiency for high quality filtration with broad chemical compatibility.

No silicone is intentionally used in materials of construction or in manufacturing.

The raw materials composing these filters are FDA compliant according to CFR Title 21.

Sealing Ring:

Available in "A" - Stainless Steel, and "B" - Polypropylene

Available in "P" - Polypropylene Collar*

Performance Data

Loading Capacity

Product Model Number	123	124	125	126	128
Dirt - grams at 25 gpm (5.6 cu m/hr)	125	121	146	155	351
Mineral Oil - grams at saturation	1385	2280	2050	1640	2845

*Only on 128 grade.



Loading: The data above shows typical loading capacities of the different micron rated filters. Loading capacity is determined by challenging a filter with a dispersion of silica test dust in water at the recommended flow rate. Pressure drop is monitored and testing is terminated at 35 psid (2.4 bar). The loading capacity reported is the dry weight gain of the bag.

Particle Removal Efficiency (microns)


Product Number	123	124	125	126	128
Efficiency @95%	1.5	2.5	7.5	10.0	34.0
Efficiency @90%	1.3	1.3	6.5	8.0	29.0
Efficiency @75%	0.9	1.0	2.5	7.0	21.0
Efficiency @50%	<0.7	<1.0	<1.0	4.5	7.0

Efficiency: The Series 100 High Performance Filter Bags are rated using a silica test challenge in water at 25 gpm (5.7 cu m/hr). The results reported are typical initial efficiencies taken within ten minutes of the start of the test and are cumulative data.

Operating Conditions

Maximum Operating Temperature:	180° F (82° C)
Recommended Flow (in water):	25 gpm (5.7 cu m/hr)
Suggested Maximum Flow (in water):	50 gpm (11 cu m/hr)
Suggested Maximum Differential Pressure:	35 psid (2.4 bar)

Clean Pressure Drop Versus Flow Rate (psid)



Pressure Drop: The Series 100 High Performance Filter Bags have low initial pressure drop (Δp) in water as the chart indicates. The chart includes the pressure drop of a typical single vessel to assist you in sizing your filter system.

Disposal

Disposal of used filter bags must comply with applicable federal, state and local laws and regulations.

Product Specifications

Product Model Number	Sealing Ring Material	Micron Rating Initial Efficiency	Part Number	Length	Bags per Case
113A	Stainless Steel	1.5 micron @ 95%	70-0202-3727-0	110 Series #1 Size: 16 in (41 cm)	10
113B	Polypropylene		70-0202-2776-8		
113D	Stainless Steel		70-0202-3728-8		
114A	Stainless Steel	2.5 micron @ 95%	70-0202-3729-6		
114B	Polypropylene		70-0202-2779-2		
114D	Stainless Steel		70-0202-3730-4		
115A	Stainless Steel	7.5 micron @ 95%	70-0202-3731-2		
115B	Polypropylene		70-0202-2782-6		
115D	Stainless Steel		70-0202-2783-4		
116A	Stainless Steel	10 micron @ 95%	70-0202-3732-0		
116B	Polypropylene		70-0202-2785-9		
116D	Stainless Steel		70-0202-3733-8		
118A	Stainless Steel	34 micron @ 95%	70-0202-3734-6		
118B	Polypropylene		70-0202-2788-3		
118D	Stainless Steel		70-0202-2789-1		
123A	Stainless Steel	1.5 micron @ 95%	70-0202-2790-9	120 Series #2 Size: 32 in (81 cm)	10
123B	Polypropylene		70-0202-3736-1		
123D	Stainless Steel		70-0202-3737-9		
124A	Stainless Steel	2.5 micron @ 95%	70-0202-3738-7		
124B	Polypropylene		70-0202-3739-5		
124D	Stainless Steel		70-0202-3740-3		
125A	Stainless Steel	7.5 micron @ 95%	70-0202-3874-0		
125B	Polypropylene		70-0202-3741-1		
125D	Stainless Steel		70-0202-2798-2		
126A	Stainless Steel	10 micron @ 95%	70-0202-3742-9		
126B	Polypropylene		70-0202-3743-7		
126D	Stainless Steel		70-0202-2801-4		
128A	Stainless Steel	34 micron @ 95%	70-0202-3744-5		
128B	Polypropylene		70-0202-3745-2		
128D	Stainless Steel		70-0202-2804-8		
128P	Polypropylene Collar		70-0202-9267-1		8

Sealing Ring Diameters: "A" Versions: 7.03" (17.9 cm), "B" Versions: 7.20" (18.3cm), "C" Versions: 7.00" (17.8 cm)

Important Notice

The information described in this literature is accurate to the best of our knowledge. A variety of factors, however, can affect the performance of the Product(s) in a particular application, some of which are uniquely within your knowledge and control. **INFORMATION IS SUPPLIED UPON THE CONDITION THAT THE PERSONS RECEIVING THE SAME WILL MAKE THEIR OWN DETERMINATION AS TO ITS SUITABILITY FOR THEIR USE. IN NO EVENT WILL 3M PURIFICATION INC. BE RESPONSIBLE FOR DAMAGES OF ANY NATURE WHATSOEVER RESULTING FROM THE USE OF OR RELIANCE UPON INFORMATION.**

It is your responsibility to determine if additional testing or information is required and if this product is fit for a particular purpose and suitable in your specific application.

3M PURIFICATION INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY OTHER NATURE HEREUNDER WITH RESPECT TO INFORMATION OR THE PRODUCT TO WHICH INFORMATION REFERS.

Limitation of Liability

3M Purification Inc. will not be liable for any loss or damage arising from the use of the Product(s), whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation may not apply to you.



3M Purification Inc.
400 Research Parkway
Meriden, CT 06450
U.S.A.
Phone (800) 243-6894
(203) 237-5541
Fax (203) 630-4530
www.3mpurification.com

3M is a trademark of 3M Company.
© 2013 3M Company. All rights reserved.
Please recycle. Printed in U.S.A.
70070812873 REV 0213b

Your Local Distributor:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000001843](#) [7000029498](#) [7000029513](#) [7000051209](#) [7000051210](#) [7000051248](#) [7000051249](#) [7000051637](#)
[7000125825](#) [7000125850](#) [7000125852](#) [7010314163](#) [7010339883](#) [7010380788](#) [7100006219](#) [7100007394](#)
[7100085491](#)