

## SN62/PB36/AG2 SOLDER ALLOY

### FEATURES

- Liquidus 179°C (354°F)
- High Purity
- Low Dross
- High Fluidity
- Complies with IPC J-STD-006

### DESCRIPTION

Sn62/Pb36/Ag2 is a eutectic alloy with a melting point of 179°C (354°F). Sn62/Pb36/Ag2 AIM Electropure™ solder is manufactured using responsibly sourced, high purity elements resulting in low dross, high fluidity solder. AIM Sn62/Pb36/Ag2 can lower costs, increase productivity and reduce defects.

### AVAILABILITY


Sn62/Pb36/Ag2 Electropure is available in 1.1 kg (2.5 lb) bars, 3 kg AIM Safety Bar and Solid Wire. Sn62/Pb36/Ag2 Electropure is also available in AIM flux cored wire solder and solder paste.

### TYPICAL ALLOY COMPOSITION

Typical Alloy Composition (%)		
Sn: 62.0	Pb: 36.0	Ag: 2.0

### TYPICAL MELTING TEMPERATURE

Melting Temperature
179°C (354°F) Eutectic



### HANDLING & STORAGE

Preparation	Time	Temperature
Shelf Life	Indefinite	Room Temperature

Indefinite shelf life applies to solid solder. For other product categories, refer to product specific TDS. Consult AIM Sn62/Pb36/Ag2 Electropure SDS for additional handling procedures and precautions.

### FLUX COMPATIBILITY

Sn62/Pb36/Ag2 Electropure bar solder is compatible with all RMA, no clean and water soluble electronic grade fluxes.

### CLEANING

Refer to data sheets provided by the flux manufacturer.

### SAFETY

Use with adequate ventilation and proper personal protective equipment. Refer to the accompanying Safety Data Sheet for any specific emergency information. Do not dispose of any hazardous materials in non-approved containers.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AIM Solder:](#)

[54068](#)