

1. SPECIFICATIONS

AMF-N60C50-NA




01	Sensitivity	-50±3dB (0dB=1V/Pa,1KHz)
02	Standard Operation Voltage	2.0 V
03	Output Impedance	2.2 KΩ
04	Directivity	Noise Canceling
05	Frequency Range	100 - 10K Hz
06	Max. Operation Voltage	10V
07	Current Consumption	Max.0.5mA
08	Sensitivity Reduction	Within -3dB 0dB=1V/Pa,1KHz Vs=2.0to 1.5V
09	S/N Ratio	≥50dB
10	Sound Pressure Level	110 dB
11	Operating Temperature	-20~+60°C
12	Storage Temperature	-25~+70°C

REV NO.

REVISION NOTE

APPROVAL

DATE


 $\phi 6$


Term.1(+)

Term.2(-)

RoHS

TITLE: MICROPHONE

DRAWN: Jack 2019/11/01

SCALE: 5:1 SHEET: 1 of 1

PART NO. AMF-N60C50-NA

DESIGNED: R & D OF AAT

UNITS: mm

DWG NO. F6050NL-B

CHECKED:

TOLERANCE ± 0.3

APPROVAL:

UNLESS OTHERWISE SPECIFIED:

ONE PLACE DECIMAL $\pm$ ***TWO PLACE DECIMAL $\pm$ ***THREE PLACE DECIMAL $\pm$ ***

MATERIAL: AL



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AATC:](#)

[AMF-N60C50-NA](#)