

NYLON-FULLY INSULATED DOUBLE CRIMP FEMALE DISCONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	3	4	7	10	15	20	24

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: NYLON TERMINAL MATERIAL: BRASS


INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL

TERMINAL BARREL I.D.:

22-16 A.W.G.: C=1.7mm 16-14 A.W.G.: C=2.3mm 12-10 A.W.G.: C=3.4mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	NEMA TAB	DIMENSION ^{inch} mm						FIG	CRIMPING TOOL	Q'TY BOX
			W	F	L	B	D	T			
22-16 A.W.G. 0.5-1.5 mm ²	FDFNYD1-110(5)	.020×.110 (0.5×2.8)	.126 3.2	.256 6.5	.768 19.5	.433 11.0	.157 4.0	.012 0.3	1	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:RED	1000
	FDFNYD1-110(8)	.032×.110 (0.8×2.8)									1000
	FDFNYD1-187(5)	.020×.187 (0.5×4.75)	.197 5.0	.252 6.4	.795 20.2			.014 0.35	2		1000
	FDFNYD1-187(8)	.032×.187 (0.8×4.75)									1000
	FDFNYD1-205(5)	.020×.205 (0.5×5.2)	.224 5.7	.228 5.8	.846 21.5			.016 0.4	1		1000
	FDFNYD1-205(8)	.032×.205 (0.8×5.2)									1000
	FDFNYD1-250	.032×.250 (0.8×6.35)	.260 6.6	.295 7.5	.846 21.5			.016 0.4	1		1000
16-14 A.W.G. 1.5-2.5 mm ²	FDFNYD2-187(5)	.020×.187 (0.5×4.75)	.197 5.0	.252 6.4	.795 20.2	.433 11.0	.197 5.0	.014 0.35	2	IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:BLUE	1000
	FDFNYD2-187(8)	.032×.187 (0.8×4.75)									1000
	FDFNYD2-205(5)	.020×.205 (0.5×5.2)	.224 5.7	.228 5.8	.846 21.5			.014 0.35	1		1000
	FDFNYD2-205(8)	.032×.205 (0.8×5.2)									1000
	FDFNYD2-250	.032×.250 (0.8×6.35)	.260 6.6	.295 7.5	.846 21.5			.016 0.4	1		1000
12-10 A.W.G. 4-6 mm ²	FDFNYD5-250	.032×.250 (0.8×6.35)	.260 6.6	.295 7.5	.953 24.2	.512 13.0	.256 6.5	.016 0.4	2	IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[FDFNYD1-110\(5\)](#) [FDFNYD1-110\(8\)](#) [FDFNYD1-187\(5\)](#) [FDFNYD1-187\(8\)](#) [FDFNYD1-250](#) [FDFNYD2-187\(5\)](#)
[FDFNYD2-187\(8\)](#) [FDFNYD2-250](#) [FDFNYD5-250](#)