


VINYL-INSULATED LOCKING SPADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL
INSULATION COLOR:

 22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■
TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	LSVB1-3.2	LSV1-3.2	#4	.125 3.2	.252 6.4	.256 6.5	.827 21.0	.394 10.0	.157 4.0	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR: RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR: RED	1000
	LSVB1-3.7	LSV1-3.7	#6	.146 3.7									1000
	LSVBS1-4	LSVS1-4	#8	.169 4.3									1000
	LSVBL1-4	LSVL1-4	#8	.169 4.3									1000
	LSVBS1-5	LSVS1-5	#10	.209 5.3									1000
	LSVBL1-5	LSVL1-5	#10	.209 5.3									1000
16-14 A.W.G. 1.5-2.5 mm ²	LSVB2-3.2	LSV2-3.2	#4	.126 3.2	.236 6.0	.256 6.5	.827 21.0	.394 10.0	.177 4.5	.091 2.3	.031 0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR: BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR: BLUE	1000
	LSVB2-3.7	LSV2-3.7	#6	.146 3.7									1000
	LSVBL2-3.7	LSVL2-3.7	#6	.146 3.7									1000
	LSVB2-4	LSV2-4	#8	.169 4.3									1000
	LSVBL2-4	LSVL2-4	#8	.169 4.3									1000
	LSVBS2-5	LSVS2-5	#10	.209 5.3									1000
	LSVBL2-5	LSVL2-5	#10	.209 5.3									1000
	LSVB2-6	LSV2-6	1/4	.252 6.4									1000
12-10 A.W.G. 4-6 mm ²	LSVBS5-3.7	LSVS5-3.7	#4	.146 3.7	.307 7.8	.276 7.0	.992 25.2	.512 13.0	.252 6.4	.134 3.4	.039 1.0	IZUMI MODEL 5 WITH DIE INDEX COLOR: YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR: YELLOW	500
	LSVB5-3.7	LSV5-3.7	#6	.146 3.7									500
	LSVB5-4	LSV5-4	#8	.169 4.3									500
	LSVB5-5	LSV5-5	#10	.209 5.3									500
	LSVB5-6	LSV5-6	1/4	.252 6.4									500

(UL) c(UL) ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[LSVB1-3.7](#) [LSVB2-4](#) [LSVB5-5](#) [LSVBS2-5](#)