

NYLON-FULLY INSULATED DOUBLE CRIMP PIGGY BACK DISCONNECTORS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	3	4	7	10	15	20	24

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON TERMINAL MATERIAL: BRASS
INSULATION COLOR:

 22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW
DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL
TERMINAL BARREL I.D.:

22-16 A.W.G.: C=1.7mm 16-14 A.W.G.: C=2.3mm 12-10 A.W.G.: C=3.4mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	NEMA TAB	DIMENSION inch mm								CRIMPING TOOL	Q'TY BOX
			W	W1	F	F1	L	B	D	T		
22-16 A.W.G. 0.5-1.5 mm ²	PBDFNYD1-250	.032 × .250 (0.8 × 6.35)	.260 6.6	.250 6.35	.315 8.0	.323 8.2	.846 21.5	.433 11.0	.157 4.0	.016 0.4	IZUMI MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	PBDFNYD2-250	.032 × .250 (0.8 × 6.35)	.260 6.6	.250 6.35	.315 8.0	.323 8.2	.846 21.5	.433 11.0	.197 5.0	.016 0.4	IZUMI MODEL 34 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:BLUE	1000
12-10 A.W.G. 4-6 mm ²	PBDFNYD5-250	.032 × .250 (0.8 × 6.35)	.260 6.6	.250 6.35	.315 8.0	.323 8.2	.945 24.0	.512 13.0	.256 6.5	.016 0.4	IZUMI MODEL 5 OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500

(UL) c(UL) ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[PBDFNYD1-250](#) [PBDFNYD2-250](#)