


NYLON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	4	2
AMP.	125	170

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON
INSULATION COLOR:

 4 A.W.G.: YELLOW 2 A.W.G.: RED
TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
4 A.W.G. 22 mm ²	RNYBL22-10		3/8	.413 10.5	.689 17.5	.630 16.0	1.917 48.7					K.S. MODEL KST-HDC38A WITH DIE INDEX :INS(mm)22	200
	RNYB22-11		7/16	.453 11.5	.866 22.0	.776 19.7	2.146 54.5						200
	RNYB22-12		1/2	.512 13.0									200
	RNYB22-14		9/16	.591 15.0				.945 24.0	.512 13.0	.303 7.7	.067 1.7		200
	RNYB22-16		5/8	.669 17.0									200
	RNYB22-18		11/16	.748 19.0	1.181 30.0	.953 24.2	2.480 63.0						200
	RNYB22-20		3/4	.827 21.0									200
	RNYB22-22		7/8	.906 23.0									200
2 A.W.G. 38 mm ²	RNYB38-5		#10	.209 5.3	.602 15.3	.685 17.4	2.047 52.0					K.S. MODEL KST-HDC38A WITH DIE INDEX :INS(mm)38	100
	RNYBS38-6		1/4	.252 6.4									100
	RNYBL38-6		1/4	.252 6.4	.866 22.0	.697 17.7	2.193 55.7						100
	RNYBS38-8		5/16	.331 8.4	.602 15.3	.685 17.4	2.047 52.0						100
	RNYBL38-8		5/16	.331 8.4	.866 22.0	.697 17.7	2.193 55.7						100
	RNYBS38-10		3/8	.413 10.5	.602 15.3	.685 17.4	2.047 52.0						100
	RNYBL38-10		3/8	.413 10.5									100
	RNYB38-11		7/16	.453 11.5	.866 22.0	.697 17.7	2.193 55.7	1.063 27.0	.571 14.5	.370 9.4	.071 1.8		100
	RNYB38-12		1/2	.512 13.0									100
	RNYB38-13		9/16	.551 14.0									100
	RNYB38-14		9/16	.591 15.0									100
	RNYB38-16		5/8	.669 17.0									100
	RNYB38-18		11/16	.748 19.0	1.181 30.0	.917 23.3	2.560 65.0						100
	RNYB38-20		3/4	.827 21.0									100
	RNYB38-24		15/16	.984 25.0									100



ALL LISTED

* : ADDITIONAL CERTIFIED

■ : 90D available

Products can be bend to 90-degrees angle.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[RNYB22-12](#) [RNYBS38-10](#) [RNYBS38-6](#) [RNYBS38-8](#)