


File Name:

1. SPECIFICATION



AR-1332DA-21W1-LF

ITEMS.		SPECIFICATIONS
01	Type	Dynamic 13mm receiver unit
02	Sensitivity (S.P.L)	115dB $\pm$ 3 dB at 1kHz 180mV with IEC 318 coupler
03	Impedance.	32 Ohm $\pm$ 15% at 1KHz
04	Magnet Field Intensity.	Axial – dB , Radial –dB at 1KHz
05	Nominal Input Power	10mW
06	Max. Input Power.	Must be normal at a white noise , 26mW(900mV) for 1 minute.
07	Total Harmonics Distortion	Max 5 % at 1K Hz.

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



WIRE : UL1571 , AWG32 .



MATERIAL

HOUSING : METAL

DIAPHRAGM : PEI

TITLE: DYNAMIC RECEIVER		DRAWN: JOHN	04/22/2005	SCALE: 3:1	SHEET: 1 of 1
PART NO. AR-1332DA-21W1-LF		DESIGNED: R & D OF AAT		UNITS: mm	
DWG NO. DTR-1085		CHECKED:		TOLERANCE ± 0.2	
		APPROVAL:		UNLESS OTHERWISE SPECIFIED:	
		MATERIAL: *****		ONE PLACE DECIMAL ± ***	
				TWO PLACE DECIMAL ± ***	
				THREE PLACE DECIMAL ± ***	



苙翔科技股份有限公司
ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

[AR-1332DA-21W1-LF](#)