



1. SPECIFICATION

AD-85D4F

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	3.6	 Standard state, standard drive circuit. Square wave 1/2 duty.
02	Operating Voltage	V	2.0 ~ 5.0	
03	Consumption Current	mA Max.	100	
04	Sound pressure level (Distance at 10cm)	dB(A) Min.	87	Rated voltage, rated frequency.
05	Direct Current Resistance	Ω	16 $\pm$ 3	
06	Rated Frequency	Hz	4000	
07	Operating Temp.	°C	-40 ~ +105	
08	Storage Temp.	°C	-40 ~ +105	
09	Weight	g	0.5 $\pm$ 0.2	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



RoHS

TITLE: SOUND TRANSDUCER (SMD)		DRAWN: Zack	2020/11/10	SCALE: 1:1	SHEET: 1 : 1
PART NO. AD-85D4F		DESIGNED: R & D OF AAT		UNITS: mm	
DWG NO. SMD-085030F-03640R16-L		CHECKED:		TOLERANCE ± 0.5	
		APPROVAL:		FIRST ANGLE PROJECTION	
REV		MATERIAL: LCP			



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

AD-8504-CQ10-LF