

## 1. SPECIFICATION

AK-2808AB-18

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diameter 28 mm	
03	Rated Input Power	0.3 W	
04	Max. Input Power	0.5 W for 1 minute	
05	Impedance	8 Ω ± 15% at 2 KHz 1V	
06	Resonance Frequency (Fo)	750 Hz ± 20% at Fo, 1V	
07	Sound pressure level	90 dB(0.1W/0.1M) ± 3 dB	at AVE 0.8, 1.0, 1.2, 1.6 KHz.
		94 dB(0.3W/0.1M) ± 3 dB	
08	Frequency Range	Fo – 7 K Hz	
09	Total Harmonics Distortion	Max 10 % at 1 KHz, 1.5V.	
10	Voice Coil	Diameter 10.5 mm	
11	Magnet	Rare earth permanent ( NdFeB ) magnet Φ9 x 1.5 mm	
12	Weight	5.2 g ± 0.5 g	
13	Appearance	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc.	
14	Operation Test	Must be normal at program source 0.3 W	
15	Buzz, Rattle, etc.	Should not be audible at 1.55 V sine wave between Fo to 20KHz	
16	Polarity	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front.	
17	Terminal Strength	Capable of withstand 1kg load for 15 seconds without resulting in any damage or rejection.	
18	Temperature	Operating temperature: -20°C to +60°C	
		Storage temperature: -30°C to +70°C	




RoHS

REV NO.

REVISION NOTE

APPROVAL

DATE



RoHS

TITLE: DYNAMIC SPEAKER

DRAWN: Jack 2014/03/07

SCALE: 2:1 SHEET: 1:1

PART NO. AK-2808AB-18

DESIGNED: R&amp;D OF AAT

UNITS: mm

DWG NO. UGS2808-16-02

2

CHECKED:

TOLERANCE  $\pm 0.5$ 

APPROVAL:

UNLESS OTHERWISE SPECIFIED:

MATERIAL: \*\*\*\*\*

ONE PLACE DECIMAL  $\pm$  \*\*\*TWO PLACE DECIMAL  $\pm$  \*\*\*THREE PLACE DECIMAL  $\pm$  \*\*\*

ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

AK-2808AB-18