


1. SPECIFICATIONS

AMF-N97C52-NA

01	Sensitivity	-52±3dB (0dB=1V/Pa,1KHz)
02	Standard Operation Voltage	4.5 V
03	Output Impedance	2.2 KΩ
04	※Directivity	Unidirectional
05	Frequency Range	100 - 10K Hz
06	Max. Operation Voltage	10V
07	Current Consumption	Max.0.5mA
08	Sensitivity Reduction	Within -3dB (0dB=1V/Pa,1KHz ,Vs=4.5 reduced to 4.0 V)
09	S/N Ratio	≥58dB
10	Sound Pressure Level	110 dB
11	Operating Temperature	-20~+60°C
12	Storage Temperature	-25~+70°C

※ For noise-cancelling use, please refer to unidirectional or bidirectional types.

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



RoHS

TITLE: MICROPHONE		DRAWN: Jason	2010/04/01	SCALE: 5:1	SHEET: 1 of 1
PART NO. AMF-N97C52-NA	1	DESIGNED: R & D OF AAT		UNITS: mm	
DWG NO. F9750NL		CHECKED:		TOLERANCE ± 0.3	
		APPROVAL:		FIRST ANGLE PROJECTION	
	REV	MATERIAL: *****			



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AATC:](#)

[AMF-N97C52-NA](#)