

Electronic Component Solar Panels

Indoor Light Series

The Indoor Light Series opens new opportunities for developing remote power solutions in low light and indoor applications. These panels provide energy collection at light levels down to 200 lux and below, making them useful for almost any indoor environment.

Whether you need advice on battery sizing and chemistry or circuit design using any of the leading energy-harvesting chips on the market today, we can help. We also offer development kits that will take you from IoT concept to product faster.

Looking for a custom Electronic Component Solar Panel? We offer custom sizes, voltages, encapsulations and substrates. If you are working on indoor applications we can provide additional support in designing your solution.

Contact us at www.powerfilmsolar.com to learn more.

INP1.2-12x34

Electrical Specifications:
Max Voc all light levels - 1.9V

200 Lux

Power: 0.010mW
Operating Voltage: 0.8V
Operating Current: 0.012mA

1000 Lux


Power: 0.065mW
Operating Voltage: 1.1V
Operating Current: 0.059mA

Physical Specifications:

Dimensions:
34.0 x 12.0 (mm)
1.338 x 0.472 (in)
Weight: 0.004oz / 0.13g



IV Curve



INP2.4-10x94T

Electrical Specifications:
Max Voc all light levels - 3.7V

200 Lux

Power: 0.033mW
Operating Voltage: 1.6V
Operating Current: 0.021mA

1000 Lux


Power: 0.219mW
Operating Voltage: 2.1V
Operating Current: 0.105mA

Physical Specifications:

Dimensions:
94.0 x 10.0 (mm)
3.7 x 0.393 (in)
Weight: 0.01oz / 0.25g



IV Curve



PowerFilm[®]

MADE IN THE USA

SOLAR

INP3.6-24x44T

Electrical Specifications:

Max Voc all light levels - 5.5V

200 Lux

Power: 0.031mW

Operating Voltage: 2.4V

Operating Current: 0.013mA

1000 Lux

Power: 0.204mW

Operating Voltage: 3.2V

Operating Current: 0.063mA

Physical Specifications:

Dimensions:


44.0 x 24.0 (mm)

1.732 x 0.944 (in)

Weight: 0.01oz / 0.36g



IV Curve



INP3.6-12x310

Electrical Specifications:

Max Voc all light levels - 5.5V

200 Lux

Power: 0.150mW

Operating Voltage: 2.4V

Operating Current: 0.062mA

1000 Lux

Power: 0.982mW

Operating Voltage: 3.2V

Operating Current: 0.307mA

Physical Specifications:

Dimensions:


310.0 x 11.86 (mm)

12.204 x 0.466 (in)

Weight: 0.03oz / 0.84g



IV Curve



LL200-2.4-37

Electrical Specifications:

Max Voc all light levels - 3.7V

200 Lux

Power: 0.068mW

Operating Voltage: 1.6V

Operating Current: 0.043mA

1000 Lux

Power: 0.449mW

Operating Voltage: 2.1V

Operating Current: 0.214mA

Physical Specifications:

Dimensions:


54.0 x 36.5 (mm)

2.13 x 1.44 (in)

Weight: 0.02oz / 0.55g



IV Curve



LL200-2.4-75

Electrical Specifications:

Max Voc all light levels - 3.7V

200 Lux

Power: 0.289mW

Operating Voltage: 1.6V

Operating Current: 0.181mA

1000 Lux

Power: 1.899mW

Operating Voltage: 2.1V

Operating Current: 0.904mA

Physical Specifications:

Dimensions:


94.0 x 73.0 (mm)

3.70 x 2.87 (in)

Weight: 0.04oz / 1.20g



IV Curve



PowerFilm[®]

MADE IN THE USA

SOLAR

LL200-3-37

Electrical Specifications:

Max Voc all light levels - 4.6V

200 Lux

Power: 0.166mW

Operating Voltage: 2.1V

Operating Current: 0.079mA

1000 Lux

Power: 1.089mW

Operating Voltage: 2.6V

Operating Current: 0.419mA


Physical Specifications:

Dimensions:


114.0 x 36.5 (mm)

4.49 x 1.44 (in)

Weight: 0.04oz / 1.13g



IV Curve



LL200-3.6-75

Electrical Specifications:

Max Voc all light levels - 5.5V

200 Lux

Power: 0.206mW

Operating Voltage: 2.4V

Operating Current: 0.086mA

1000 Lux

Power: 1.354mW

Operating Voltage: 3.2V

Operating Current: 0.423mA


Physical Specifications:

Dimensions:


74.0 x 73.0 (mm)

2.91 x 2.87 (in)

Weight: 0.05oz / 1.42g



IV Curve



LL200-4.8-37

Electrical Specifications:

Max Voc all light levels - 7.4V

200 Lux

Power: 0.133mW

Operating Voltage: 3.2V

Operating Current: 0.041mA

1000 Lux

Power: 0.871mW

Operating Voltage: 4.2V

Operating Current: 0.207mA


Physical Specifications:

Dimensions:


94.0 x 36.5 (mm)

3.70 x 1.44 (in)

Weight: 0.03oz / 0.88g



IV Curve



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PowerFilm:](#)

[INP1.2-12x34](#) [INP3.6-12x310](#) [INP3.6-24x44T](#) [INP2.4-10x94T](#)