

# INFRARED THERMOMETER WITH LASER

IR1



-4°F –  
752°F  
-20°C –  
400°C



°F °C



APO

HOLD



2m







CE



**KLEIN  
TOOLS** 



**10:1**  
Distance-to-Spot Ratio

Measurement	IR1
Targeting Laser	 ●
Temperature	 -4° – 752° F (-20° – 400° C)
Backlight	 ●
Auto Power-Off	 ●
Data Hold	 ●
<b>Durability</b>	
Drop Protection	 6.6 ft. (2 m)

## INFRARED THERMOMETER WITH LASER

Klein Tools IR1 is an easy-to-use, durable infrared (IR) thermometer. Simply point targeting laser on area to measure, pull the trigger, and read measurement on the display. The IR1 features 10:1 optical resolution, a backlit LCD, and a wide temperature measurement range of -4 to 752°F (-20 to 400°C). Built to withstand a 6.6 ft (2 m) drop test.

Targeting Laser


IR Temperature Sensor

Trigger

LCD Display  
with Data Hold

Battery  
Compartment  
(in handle)

Includes:



This meter is configured with a 10:1 optical resolution (distance-to-spot ratio). The distance-to-spot ratio defines the size of the measurement area relative to the distance between the measurement location and the IR sensor.



**CAUTION:** Reflective materials may be hotter than indicated.

**CAUTION**  
LASER RADIATION:  
DO NOT STARE INTO BEAM  
Max. Output <1mW  
Wavelength: 630-670nm  
CLASS 2 LASER PRODUCT

Cat. No.	UPC 0-92644+	Description	Batteries	Height	Width	Length	Weight
IR1	69292-5	Infrared Thermometer with Laser, 10:1	1 x 9V	4.14" (10.5 cm)	1.24" (3.1 cm)	6.0" (15.3 cm)	10.3 oz (.292 g)

US Patent D791624

See our complete line of Test & Measurement Products  
[www.kleintools.com](http://www.kleintools.com)



© 2020 Klein Tools, Inc.  
Lincolnshire, IL 60069  
82910 Rev. 02/20 A



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Klein Tools:

IR1 IR1KIT