


Specifications



Type : Nickel-Metal Hydride Battery			Size : AA
Capacity ¹⁾	Typical		1650 mAh
	Minimum		1500 mAh
Nominal Voltage			1.2 V
Charging Current x Time		Fast Charge ²⁾	1650 mA x about 1.1 h
Ambient Temp.	Charge Condition	Fast Charge ²⁾	0 °C ~ + 40 °C
	Discharge Condition		0 °C ~ + 50 °C
	Storage Condition	Less than 30days	-20 °C ~ + 50 °C
		Less than 90days	-20 °C ~ + 40 °C
		Less than 1year	-20 °C ~ + 30 °C
Internal Impedance ³⁾ (after discharge to E.V.=1.0V)			Approx. 25 mΩ(at 1000Hz)
Weight ⁴⁾			Approx. 27 g
Size ⁴⁾ :(Diameter) x (Height)			14.2 (D) x 50.0 (H) mm

1)Single cell capacity under the following condition.

Charge : 165 mA × 16 h, Discharge : 330 mA(E.V.=1.0 V) at 20 °C


2)Use recommended charging system.

3)After a few charge and discharge cycles under the above 1) condition.


4)With tube.

Typical Characteristics

Charge



Discharge



YAH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Unspecified:

[HR-AAU](#) [HRAAU-ST](#)