

VINYL-INSULATED CHANGING DOWN BUTT SPLICE CONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10	8	6
AMP.	9	12	17	18	30	35	50	70	95

MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.


CONNECTOR MATERIAL: COPPER TUBULAR

INSULATION MATERIAL: VINYL

INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

8 A.W.G.: RED 6 A.W.G.: BLUE



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION inch mm				INSULATION COLOR WITH CHANGING DOWN END COLOR RING	CRIMPING TOOL	Q'TY BOX
		L	D	d1	d2			
16-14 to 22-18 A.W.G. 1.5-2.5 to 0.5-1.0 mm ²	BVT2CD1	.965 24.5	.177 4.5	.067 1.7	.091 2.3	BLUE WITH RED COLOR RING	K.S. MODEL KST2000A WITH DIE INDEX COLOR:BLUE	1000
12-10 to 22-18 A.W.G. 4-6 to 0.5-1.0 mm ²	BVT5CD1	1.220 31.0	.248 6.3	.067 1.7	.134 3.4	YELLOW WITH RED COLOR RING	K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500
12-10 to 16-14 A.W.G. 4-6 to 1.5-2.5 mm ²	BVT5CD2	1.220 31.0	.248 6.3	.091 2.3	.134 3.4	YELLOW WITH BLUE COLOR RING	K.S. MODEL KST2000A WITH DIE INDEX COLOR:YELLOW	500
8 to 16-14 A.W.G. 8 to 1.5-2.5 mm ²	BVT8CD2	1.406 35.7	.335 8.5	.091 2.3	.177 4.5	RED WITH BLUE COLOR RING	K.S. MODEL KST-HDC38A WITH DIE INDEX INS(AWG)NO.:8	200
8 to 12-10 A.W.G. 8 to 4-6 mm ²	BVT8CD5	1.406 35.7	.335 8.5	.134 3.4	.177 4.5	RED WITH YELLOW COLOR RING	K.S. MODEL KST-HDC38A WITH DIE INDEX INS(AWG)NO.:8	200
6 to 8 A.W.G. 8 to 14 mm ²	BVT14CD8	1.172 45.0	.413 10.5	.177 4.5	.232 5.9	BLUE WITH RED COLOR RING	K.S. MODEL KST-HDC38A WITH DIE INDEX INS(AWG)NO.:14	100



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[BVT14CD8](#) [BVT2CD1](#) [BVT5CD1](#) [BVT5CD2](#) [BVT8CD2](#) [BVT8CD5](#)