


DIN 46234

NON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	20	18	16	14
AMP.	5.5	7	9	12	17	18	30

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION mm						CRIMPING TOOL	Q'TY BOX		
		d2	d3	I	a	C	d1	S					
26-22 A.W.G. 0.2-0.5 mm ²	DRNBS2-0.5	#2	2.0	4.4	10.0	4.0	2.0	1.0	0.5	K.S. MODEL KSTHT-203 WITH DIE INDEX NO:(INSUL)16-22	1000		
	DRNB2-0.5	#2	2.2	5.0							1000		
	DRNB2.5-0.5	#3	2.7								1000		
	DRNB3-0.5	#4	3.2								1000		
	DRNB3.5-0.5	#6	3.7	6.0	12.0						1000		
	DRNB4-0.5	#8	4.3	6.5							1000		
	DRNB5-0.5	#10	5.3	8.0							1000		
22-16 A.W.G. 0.5-1.5 mm ²	DRNB2-1	#2	2.2	6.0	11.0	5.0	4.0	1.6	0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:1.25	1000		
	DRNB2.5-1	#3	2.7								1000		
	DRNB3-1	#4	3.2								1000		
	DRNB3.5-1	#6	3.7								1000		
	DRNBS4-1	#8	4.3	7.0	11.5						8.0	12.0	1000
	DRNB4-1	#8	4.3	12.5	1000								
	DRNBS5-1	#10	5.3	10.0	13.0						1000		
	DRNB5-1	#10	5.3								1000		
	DRNB6-1	1/4	6.5								15.0	1000	
	DRNBL6-1	1/4	6.5								11.0	15.0	1000
	DRNB8-1	5/16	8.4	14.0	17.0						1000		
	DRNB10-1	3/8	10.5								1000		
	DRNBL10-1	3/8	10.5								18.0	19.0	1000
16-14 A.W.G. 1.5-2.5 mm ²	DRNB3-2.5	#4	3.2	6.0	11.0	5.0	4.5	2.3	0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:2	1000		
	DRNB3.5-2.5	#6	3.7								1000		
	DRNBS4-2.5	#8	4.3								6.8	11.6	1000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DRNB10-1](#) [DRNB2.5-0.5](#) [DRNB2.5-1](#) [DRNB2-0.5](#) [DRNB2-1](#) [DRNB3.5-0.5](#) [DRNB3.5-1](#) [DRNB3.5-2.5](#) [DRNB3-0.5](#)
[DRNB3-1](#) [DRNB3-2.5](#) [DRNB4-0.5](#) [DRNB4-1](#) [DRNB5-0.5](#) [DRNB5-1](#) [DRNB6-1](#) [DRNB8-1](#) [DRNBL10-1](#) [DRNBL6-1](#)
[DRNBS4-1](#) [DRNBS4-2.5](#) [DRNBS5-1](#)