

DIN 46237

VINYL-INSULATED (EASY ENTRY) SPADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

| | | | | | | | |
|--------|----|----|----|----|----|----|----|
| A.W.G. | 22 | 20 | 18 | 16 | 14 | 12 | 10 |
| AMP. | 9 | 12 | 17 | 18 | 30 | 35 | 50 |


MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.

INSULATION MATERIAL: VINYL

INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

TERMINAL MATERIAL: COPPER



| WIRE RANGE A.W.G. mm ² | ITEM NO. | | STUD SIZE | | DIMENSION mm | | | | | | CRIMPING TOOL | Q'TY BOX |
|---|--------------|-------------|-----------|------|--------------|------|-----|-----|------|-----|---|----------|
| | BRAZED SEAM | BUTTED SEAM | d2 | | d3 | I | d1 | d4 | a | S | | |
| 22-16 A.W.G. 0.5-1.5 mm ² | DSVEB3-1 | DSVE3-1 | #4 | 3.2 | 6.0 | 17.2 | 1.6 | 4.0 | 11.2 | 0.8 | IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED | 1000 |
| | DSVEB3.5-1 | DSVE3.5-1 | #6 | 3.7 | | | | | | | | 1000 |
| | DSVEB4-1 | DSVE4-1 | #8 | 4.3 | 6.8 | 18.2 | | | | | | 1000 |
| | DSVEBL4-1 | DSVEL4-1 | #8 | 4.3 | 8.0 | | | | | | | 1000 |
| | DSVEB5-1 | DSVE5-1 | #10 | 5.3 | 10.0 | 19.2 | | | | | | 1000 |
| | DSVEB6-1 | DSVE6-1 | 1/4 | 6.5 | 11.0 | 21.2 | | | | | | 1000 |
| 16-14 A.W.G. 1.5-2.5 mm ² | DSVEB3-2.5 | DSVE3-2.5 | #4 | 3.2 | 5.5 | 19.5 | 2.3 | 4.5 | 11.5 | 0.8 | IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE | 1000 |
| | DSVEB3.5-2.5 | DSVE3.5-2.5 | #6 | 3.7 | 6.0 | 17.5 | | | | | | 1000 |
| | DSVEB4-2.5 | DSVE4-2.5 | #8 | 4.3 | 6.8 | 18.5 | | | | | | 1000 |
| | DSVEBL4-2.5 | DSVEL4-2.5 | #8 | 4.3 | 8.0 | | | | | | | 1000 |
| | DSVEB5-2.5 | DSVE5-2.5 | #10 | 5.3 | 10.0 | 20.5 | | | | | | 1000 |
| | DSVEB6-2.5 | DSVE6-2.5 | 1/4 | 6.5 | 11.0 | 22.5 | | | | | | 1000 |
| 12-10 A.W.G. 2.5-6 mm ² | DSVEB4-6 | DSVE4-6 | #8 | 4.3 | 8.0 | 22.1 | 3.6 | 6.3 | 14.1 | 1.0 | IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW | 500 |
| | DSVEB5-6 | DSVE5-6 | #10 | 5.3 | 10.0 | 23.1 | | | | | | 500 |
| | DSVEB6-6 | DSVE6-6 | 1/4 | 6.5 | 11.0 | 24.1 | | | | | | 500 |
| | DSVEB8-6 | DSVE8-6 | 5/16 | 8.4 | 14.0 | 27.1 | | | | | | 500 |
| | DSVEB10-6 | DSVE10-6 | 3/8 | 10.5 | 18.0 | 29.1 | | | | | | 500 |

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DSVEB3.5-1](#) [DSVEB3.5-2.5](#) [DSVEB3-1](#) [DSVEB3-2.5](#) [DSVEB4-1](#) [DSVEB4-2.5](#) [DSVEB4-6](#) [DSVEB5-1](#) [DSVEB5-2.5](#) [DSVEB5-6](#) [DSVEB6-6](#)