

VINYL-INSULATED DOUBLE CRIMP FEMALE DISCONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22
AMP.	2	2	3


MAXIMUM ELECTRICAL RATING: 75°C 300 VOLTS MAX.

INSULATION MATERIAL: VINYL

INSULATION COLOR: 26-22 A.W.G.: YELLOW

DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL

TERMINAL BARREL I.D.: 26-22 A.W.G.: C=1.0mm



WIRE RANGE A.W.G. mm²	ITEM NO.	NEMA TAB	DIMENSION inch mm						FIG	CRIMPING TOOL	Q'TY BOX
			W	F	L	B	D	T			
26-22 A.W.G. 0.2-0.5 mm²	FDD0.5-110(5)	⊙	.126 3.2	.252 6.4	.630 16.0	.315 8.0	.126 3.2	.010 0.25	1	K.S. MODEL LY8-067 WITH DIE INDEX NO:0.5	1000
	FDD0.5-110(8)	⊙							2		1000

VINYL-INSULATED DOUBLE CRIMP FEMALE DISCONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16
AMP.	3	4	7	10


MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: VINYL TERMINAL MATERIAL: BRASS

INSULATION COLOR: 22-16 A.W.G.: RED

DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL

TERMINAL BARREL I.D.: 22-16 A.W.G.: C=1.7mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	NEMA TAB	DIMENSION ^{inch} mm						CRIMPING TOOL	Q'TY BOX
			W	F	L	B	D	T		
22-16 A.W.G. 0.5-1.5 mm ²	FDD1-110(5)	* .020 × .110 (0.5 × 2.8)	.126 3.2	.256 6.5	.748 19.0	.413 10.5	.157 4.0	.012 0.3	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A WITH DIE INDEX COLOR:RED	1000
	FDD1-110(8)	* .032 × .110 (0.8 × 2.8)								1000
	FDD1-187(5)	* .020 × .187 (0.5 × 4.75)	.197 5.0	.252 6.4	.764 19.4			.014 0.35		1000
	FDD1-187(8)	* .032 × .187 (0.8 × 4.75)								1000
	FDD1-205(5)	.020 × .205 (0.5 × 5.2)	.224 5.7	.228 5.8	.760 19.3			1000		
	FDD1-205(8)	.032 × .205 (0.8 × 5.2)						1000		
	FDD1-250	* .032 × .250 (0.8 × 6.35)	.260 6.6	.295 7.5	.819 20.8			.016 0.4		1000
	FDD1-312	⊙ .032 × .315 (0.8 × 8.0)	.323 8.2	.394 10.0	.965 24.5					1000



ALL LISTED

⊙ : NOT UL AND C-UL LISTED

* : ADDITIONAL Ⓢ CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[FDD0.5-110\(5\)](#) [FDD0.5-110\(8\)](#) [FDD1-110\(5\)](#) [FDD1-110\(8\)](#) [FDD1-187\(5\)](#) [FDD1-187\(8\)](#) [FDD1-205\(5\)](#) [FDD1-250](#)