

VINYL-INSULATED (MOLDED EASY ENTRY) LOCKING SPADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50


MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: VINYL

INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} / _{mm}							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm²	LSVYB1-3.2	LSVY1-3.2	#4	.126 3.2	.252 6.4							IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
	LSVYB1-3.7	LSVY1-3.7	#6	.146 3.7									1000
	LSVYBS1-4	LSVYS1-4	#8	.169 4.3	.283 7.2								1000
	LSVYBL1-4	LSVYL1-4	#8	.169 4.3	.319 8.1								1000
	LSVYBS1-5	LSVYS1-5	#10	.209 5.3									1000
	LSVYBL1-5	LSVYL1-5	#10	.209 5.3	.374 9.5								1000
16-14 A.W.G. 1.5-2.5 mm²	LSVYB2-3.2	LSVY2-3.2	#4	.126 3.2	.236 6.0							IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
	LSVYB2-3.7	LSVY2-3.7	#6	.146 3.7									1000
	LSVYBL2-3.7	LSVYL2-3.7	#6	.146 3.7	.283 7.2								1000
	LSVYB2-4	LSVY2-4	#8	.169 4.3									1000
	LSVYBL2-4	LSVYL2-4	#8	.169 4.3	.319 8.1								1000
	LSVYBS2-5	LSVYS2-5	#10	.209 5.3									1000
	LSVYBL2-5	LSVYL2-5	#10	.209 5.3	.366 9.3								1000
	LSVYB2-6	LSVY2-6	1/4	.252 6.4									1000
12-10 A.W.G. 4-6 mm²	LSVYBS5-3.7	LSVYS5-3.7	#6	.146 3.7	.307 7.8							IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500
	LSVYB5-3.7	LSVY5-3.7	#6	.146 3.7									500
	LSVYB5-4	LSVY5-4	#8	.169 4.3	.327 8.3	.276 7.0	.992 25.2	.512 13.0	.252 6.4	.134 3.4	.039 1.0		500
	LSVYB5-5	LSVY5-5	#10	.209 5.3	.354 9.0								500
	LSVYB5-6	LSVY5-6	1/4	.252 6.4	.472 12.0	.472 12.0	1.240 31.5						500

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[LSVY1-3.7](#) [LSVY2-3.7](#) [LSVY2-4](#) [LSVY5-5](#) [LSVYL2-5](#) [LSVYS2-5](#)