


NON-INSULATED RING TERMINALS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	250	300	350
AMP.	405	445	505

TERMINAL MATERIAL: COPPER

SURFACE TREATMENT: TIN PLATED

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE	DIMENSION inch mm								CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM		d2	W	F	L	E	D	d1	T		
250/300 MCM 150 mm ²	RNBL150-14		9/16	.591 15.0	1.417 36.0	1.417 36.0	3.189 81.0	1.063 27.0	1.047 26.6	.768 19.5	.126 3.2	IZUMI MODEL 9H-2 9H-150 12#A WITH DIE INDEX NO.:150 OR K.S. MODEL KSTP-150D WITH DIE INDEX NO.:150	25
	RNB150-16		5/8	.669 17.0		.906 23.0	2.598 66.0						25
	RNBL150-16		5/8	.669 17.0									25
	RNB150-18		11/16	.748 19.0									25
	RNB150-20		3/4	.827 21.0		1.417 36.0	3.189 81.0						25
	RNB150-22		7/8	.906 23.0									25
	RNB150-24		15/16	.984 25.0									25
	RNB150-27		1	1.102 28.0									25
300/350 MCM 180 mm ²	RNB180-6		1/4	.252 6.4	1.516 38.5			1.122 28.5	1.126 28.6	.827 21.0	.138 3.5	IZUMI MODEL 12K-1 12#A WITH DIE INDEX NO.:180 OR K.S. MODEL KSTP-150D WITH DIE INDEX NO.:180	10
	RNB180-8		5/16	.331 8.4									10
	RNB180-10		3/8	.413 10.5		.965 24.5	2.717 69.0						10
	RNB180-11		7/16	.453 11.5									10
	RNB180-12		1/2	.512 13.0									10
	RNBL180-12		1/2	.512 13.0		1.535 39.0	3.409 86.6						10
	RNB180-14		9/16	.591 15.0		.965 24.5	2.717 69.0						10
	RNB180-16		5/8	.669 17.0									10
	RNBL180-16		5/8	.669 17.0									10
	RNB180-18		11/16	.748 19.0									10
	RNB180-20		3/4	.827 21.0		1.535 39.0	3.409 86.6						10
	RNB180-22		7/8	.906 23.0									10
	RNB180-24		15/16	.984 25.0									10
	RNB180-27		1	1.102 28.0									10

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[RNB150-20](#) [RNB150-27](#) [RNB180-10](#)