


NYLON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	12	10
AMP.	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON
INSULATION COLOR:

12-10 A.W.G.: YELLOW

TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} _{mm}							CRIMPING TOOL	Q'TY BOX	
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T			
12-10 A.W.G.	RNYB5-3.2	RNY5-3.2	#4	.126 3.2	.283 7.2	.228 5.8	.886 22.5					IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500	
	RNYB5-3.7	RNY5-3.7 *	#6	.146 3.7		.240 6.1	.894 22.7						500	
	RNYBL5-3.7	RNYL5-3.7	#6	.146 3.7	.374 9.5	.327 8.3	1.024 26.0						500	
	RNYBS5-4	RNYS5-4 *	#8	.169 4.3	.283 7.2	.240 6.1	.894 22.7						500	
	RNYBL5-4	RNYL5-4 *	#8	.169 4.3	.374 9.5	.327 8.3	1.024 26.0						500	
	RNYB5-5	RNY5-5 *	#10	.209 5.3									500	
	RNYBL5-5	RNYL5-5	#10	.209 5.3	.488 12.4	.496 12.6	1.252 31.8						500	
	RNYB5-6	RNY5-6 *	1/4	.252 6.4	.472 12.0	.413 10.5	1.161 29.5						500	
	RNYBM5-6	RNYM5-6	1/4	.252 6.4		.512 13.0	1.260 32.0						500	
	RNYB5-7	RNY5-7	1/4	.291 7.4		.413 10.5	1.154 29.3						500	
4-6 mm ²	RNYBS5-8	RNYS5-8	5/16	.331 8.4	.591 15.0	.441 11.2	1.248 31.7	.512 13.0	.252 6.4	.134 3.4	.039 1.0		K.S. MODEL KST2000A	500
	RNYB5-8	RNY5-8 *	5/16	.331 8.4		.524 13.3	1.339 34.0						500	
	RNYBS5-10	RNYS5-10	3/8	.413 10.5		.441 11.2	1.248 31.7						500	
	RNYB5-10	RNY5-10 *	3/8	.413 10.5		.524 13.3	1.339 34.0						500	
	RNYB5-11	RNY5-11	7/16	.453 11.5	1.260 32.0								500	
	RNYB5-12	RNY5-12	1/2	.512 13.0		.756 19.2	.630 16.0						1.520 38.6	500
	RNYB5-13	RNY5-13	1/2	.551 14.0									500	
	RNYB5-14	RNY5-14	9/16	.591 15.0									500	
	RNYB5-16	RNY5-16	5/8	.669 17.0		.992 25.2	2.134 54.2						500	
	RNYB5-18	RNY5-18	11/16	.748 19.0									500	
RNYB5-20	RNY5-20	3/4	.827 21.0				500							



ALL LISTED

* : ADDITIONAL CERTIFIED

■ : 90D available

Products can be bend to 90-degrees angle.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[RNYB5-10](#) [RNYB5-12](#) [RNYB5-3.7](#) [RNYB5-5](#) [RNYB5-6](#) [RNYB5-8](#) [RNYBL5-4](#) [RNYBS5-4](#)