


VINYL-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16
AMP.	9	12	17	18

MAXIMUM ELECTRICAL RATING: 105 °C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL
INSULATION COLOR:

22-16 A.W.G.: RED

TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} _{mm}							CRIMPING TOOL	Q'TY BOX	
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T			
22-16 A.W.G.	RVB1-2	RV1-2	#2	.087 2.2	.217 5.5	.197 5.0	.681 17.3	.394 10.0	.157 4.0	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000	
	RVB1-2.5	RV1-2.5	#2	.095 2.4		.189 4.8	.685 17.4						1000	
	RVB1-3.2	RV1-3.2	* #4	.126 3.2		.197 5.0	.689 17.5						1000	
	RVBS1-3.7	RVS1-3.7	* #6	.146 3.7									1000	
	RVBM1-3.7	RVM1-3.7	* #6	.146 3.7	.260 6.6	.248 6.3	.764 19.4						1000	
	RVBL1-3.7	RVL1-3.7	* #6	.146 3.7	.315 8.0	.276 7.0	.819 20.8						1000	
	RVBS1-4	RVS1-4	* #8	.169 4.3	.260 6.6	.248 6.3	.764 19.4						1000	
	RVBL1-4	RVL1-4	* #8	.169 4.3	.315 8.0	.276 7.0	.819 20.8						1000	
	RVB1-5	RV1-5	* #10	.209 5.3									1000	
	RVBL1-5	RVL1-5	#10	.209 5.3	.457 11.6	.433 11.0	1.055 26.8						1.055 26.8	1000
RVB1-6	RV1-6	* 1/4	.252 6.4	1.063 27.0			1000							
RVB1-7	RV1-7	5/16	.291 7.4	1.063 27.0			1000							
RVB1-8	RV1-8	* 5/16	.331 8.4	1.055 26.8			1000							
0.5-1.5 mm ²	RVB1-10	RV1-10	* 3/8	.413 10.5	.535 13.6	.547 13.9	1.201 30.5						.031 0.8	1000
	RVBL1-10	RVL1-10	3/8	.413 10.5	.756 19.2	.630 16.0	1.402 35.6							1000
	RVB1-12	RV1-12	1/2	.512 13.0			1.394 35.4							1000
	RVB1-13	RV1-13	9/16	.551 14.0										1000
	RVB1-14	RV1-14	9/16	.591 15.0							1000			
	RVB1-16	RV1-16	5/8	.669 17.0	1.063 27.0	.827 21.0					1.744 44.3			1000
	RVB1-20	RV1-20	3/4	.827 21.0							1000			



ALL LISTED

*: ADDITIONAL



CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[RV1-10](#) [RV1-12](#) [RVL1-3.7](#) [RVL1-5](#) [RVM1-3.7](#) [RVS1-4](#) [RV1-3.2](#) [RV1-5](#) [RV1-6](#) [RV1-8](#) [RVL1-4](#) [RVS1-3.7](#)