


[Features]

- High luminance, high contrast
- Wide viewing angle
- Fast response
- LVDS interface
- Reversible-scan direction
- LED backlight*1



Pixel	1024(H) x 768(V)
Display area	304.128(H) x 228.096(V)mm (15.0 inches (38cm) diagonal)
Display color	16,777,216 colors (8-bit), 262,144 colors (6-bit)
Pixel pitch	0.297(H) x 0.297 (V)mm
Luminance	400cd/m ² (typ.)
Contrast ratio	600:1 (typ.)
Viewing angle*2	Up: 80° (typ.), Down: 80° (typ.), Left: 80° (typ.), Right: 80° (typ.)
Response time*3	8ms (typ.)
Interface	1 x LVDS 6/8-bit
Power supply voltage	LCD panel signal processing board: 3.3V, LED driver: 12.0V
Power consumption	7.1W (typ.)
Operating temperature	-20°C to +70°C
Storage temperature	-30°C to +80°C
Polarizer surface	Antiglare (AG)
Module size	326.5 (typ.) x 253.5 (typ.) x 11.8 (max.) mm
Weight	930g (typ.)
Backlight	LED backlight
LED driver	Built-in

*1: 50k hours LED life

*2: Contrast ratio ≥ 10:1

*3: Ton+Toff (10%←→90%)

*All information is subject to change without notice.

*Screen image is simulated.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tianma:

[NLB150XG02L-01](#)