

BB-400 NeuronEdge

Smart Controller for Industry 4


- Multiple connections within compact DIN mount design
- Comes with easy to use web interface
- Edge Processing with innovative industrialised Raspberry Pi
- Develop on Pi and deploy seamlessly to Industry




*Sense, sort and send your machine data
Minimize downtime, speed up response times and
maximise profits.*




- 8 Digital IO lines
- Works with common 0-30V sensors
- 1 Ethernet port for wider network
- 1 Ethernet port for LAN network
- Extendible Wi-Fi antenna
- Bluetooth - for wireless sensors
- UPS power management - prevents corruption
- Dual redundant 5-30 VDC power supply
- Raspberry Pi Compute 3+ module and Arduino processing power
- Edge processing sends relevant data to your application or the cloud
- Highly compatible open source software
- Customise with APIs and Docker containers, REST, Websockets, or .NET APIs
- Program in your favourite language or use out-of-the-box applications





| LED States | Solid Green | Flashing |
|-----------------|--|----------------------------------|
| Uplink Web | Has internet connection | Checking for internet connection |
| Uplink Link | Connected | Data |
| LAN Status | 100 Mbps link | |
| LAN Link | Connected | Data |
| Wi-Fi Web | Has internet connection | Checking for internet connection |
| Wi-Fi Link | Connected | Scanning for Wi-Fi |
| DIO 0-8 | User configurable on/off/flashing - default on when line high, off when line low | |
| A - Admin | Active session | |
| B - NFC | Available | Data |
| C - Serial Port | Open | |
| D - Bluetooth | Available | |
| Pre-charge | Charging Backup supply | |
| Running | Device is ready | |
| UPS Alert | External power loss detected - device using Backup power | |
| Stopping | Power loss unresolved - clean shutdown initiated | |

UK +44 (0)151 220 2500 // USA +1 855 958 2502
www.brainboxes.com // sales@brainboxes.com



Terminal Block Pin Outs

| Terminal Block | Pin 1 | Pin 2 | Pin 3 | Pin 4 | Pin 5 |
|------------------------------------|---------|-------|-------|-------|----------|
| Green | -V | DIO 0 | DIO 1 | DIO 2 | DIO 3 |
| Yellow | -V | DIO 4 | DIO 5 | DIO 6 | DIO 7 |
| Grey - RS232 | Sig GND | CTS | RxD | RTS | TxD |
| Grey - RS422/485 FD | Sig GND | RxD- | RxD+ | TxD+ | TxD- |
| Grey - RS485 HD | Sig GND | | | Data+ | Data- |
| Black | -V | +V A | +V B | -V | Func GND |
| Power Input +5V to +30V DC 15W Max | | | | | |

Ethernet Port Pin Outs

| PIN | FUNCTION |
|-----|-----------|
| 1 | RD+ / TD+ |
| 2 | RD- / TD- |
| 3 | TD+ / RD+ |
| 4 | NC |
| 5 | NC |
| 6 | TD- / RD- |
| 7 | NC |
| 8 | NC |

| | |
|-------------------------------|--|
| Housing | IP-20 rated non-conducting polyamide casing UL94 v-0 certified |
| Connectors | Removable, colour-coded and numbered 5 pin terminal blocks |
| Screw Terminals | 3.5mm pitch |
| Wire Thickness Power Terminal | 0.5 - 2.5 mm ² , #22 - #14 AWG |
| Wire Thickness | 0.14 - 1.3 mm ² , #26 - #16 AWG |
| Environmental | |
| Operating Temperature | -25°C to +80°C/-13°F to +176°F |
| Storage Temperature | -40°C to +80°C/-40°F to +176°F |
| Ambient Relative Humidity | 5 to 95% (non-condensing) |
| Heat Sink | Increases the achievable processing performance. Draws heat away from the Pi allowing high processor operating loads for longer www.brainboxes.com/bb-400/heatsink |

UK +44 (0)151 220 2500 // USA +1 855 958 2502
 www.brainboxes.com // sales@brainboxes.com

Power Supply

| | |
|--------------------|---|
| Power Consumption | 4 Watts typical, 15W Max dependent on application |
| Power Supply input | +5V to +30V DC, Dual Power Inputs, reverse polarity protected |
| Max Input | 35V |

| | |
|-----------|---|
| Isolation | 1500VRMS Magnetic isolation from Ethernet |
|-----------|---|

| | |
|-----|--|
| UPS | When power is interrupted the system switches to an internal backup supply for a limited time before activating a controlled shutdown (time is application dependent). |
|-----|--|

Connectivity

| | |
|----------------------|--|
| Ethernet Uplink Port | 1x RJ45 jack, 10/100Mbps autosensing, crossover autosensing (Auto MDIX) |
| Ethernet LAN Port | 1x RJ45 jack, 10/100Mbps autosensing, crossover autosensing (Auto MDIX) |
| Protection | 1500V Magnetic Isolation between ports and network |
| Wi-Fi | 802.11 b/g/n Detachable Antenna; can be used with extender cable (not included) |


| | |
|---------------------|-------------------|
| Bluetooth | 4.0 (2.1+EDR, LE) |
| Bluetooth Class | Class 1 |
| Operating Frequency | 2402MHz - 2480MHz |


| | |
|-----|---------------------------------|
| NFC | Coming soon via software update |
|-----|---------------------------------|

| | |
|-----------------|--|
| Real Time Clock | Yes, with battery backup; takes CR1220 3v lithium battery (not included) |
|-----------------|--|

Edge Processing

| | |
|------------------|---|
| Processor | Raspberry Pi Compute Module 3+, 1.2GHz quad-core Broadcom BCM2837B0, Cortex-A53 (ARMv8) 64-bit |
| RAM | 1 Gbyte LPDDR2 RAM |
| Storage | 32GB eMMC Flash memory |
| Operating System | Raspbian Lite - based on Debian Linux - latest kernel and OS version |
| Security | Latest SSH and TLS security protocols |
| Administration | Secure Web administration with user definable roles |
| Docker Support | Pre-installed with web admin interface, Customised Containers available for Node-RED |
| Configurability | Full access to secure linux command line, open system, fully configurable, custom OS can be flashed into memory if required |
| OS Compatibility | Discoverable in Windows using network tab Communicate with Device over TCP from any OS Suitable for any device with a Web Browser Raspberry Pi Android Linux |





Device administration

Administration interface

1. Secure web administration over port 9090
2. SSH using user name and passwords or SSH keys
3. USB mount the memory of the device over USB to a PC

Custom code

Multiple FAQs about writing and deploying code to the BB-400 are available on our website. Sample code is available in the following languages; .NET C#, Python, Node.js, Node-RED (visual coding interface).

Code can be deployed either by locally using secure copy (SCP) or globally by creating a Docker container.

CLI

A simple uniform interface to configure Linux system properties. Settings are stored into a yaml file which allows 1 configuration to be deployed across a fleet of devices. Brainboxes can manufacture and pre-configure BB-400 using your BB CLI yaml configuration file settings.

Docker



Is a global repository for Linux applications. Docker provides these applications in “containers” that can be downloaded through the web interface on the BB-400. Brainboxes provide a number of pre-built containers and Docker’s open source community allows you to use and contribute to even more. Each container runs like a mini virtual machine holding an application in isolation from its environment. Docker provides a good method for automatically updating containers on multiple devices in the field. www.brainboxes.com/bb-400/docker

UK +44 (0)151 220 2500 // USA +1 855 958 2502
 www.brainboxes.com // sales@brainboxes.com

Digital Channels - 8 Ports individually selectable as Inputs or Outputs

| | |
|-------------------------|--|
| Inputs | User programmable counts positive or negative transitions up to 200Hz |
| NPN/PNP | Jumper selectable pull up for NPN, active low, type sensors and pull down for PNP, active high, type sensors |
| Logic Level 0: | 0V to +1V |
| Logic Level 1: | +2V to +30V |
| Latched Inputs: | Triggered by user programmable positive or negative edges, stays true until acknowledged |
| Outputs | Default is low = off |
| Max output current | 1 channel driven: Sinks up to 0.85 Amp max Max combined load 4 Amps per BB device |
| Characteristic: | Open drain output, protected MosFET intelligent short circuit protection up to 36V |
| Max output load Voltage | 30V |
| ESD Protection | 16kV |
| IO processing | Arduino processing real time signals |
| IO Protocols | DCON ASCII (over TCP or Virtual COM port), REST, WebSocket |



The digital I/O lines run on an Arduino compatible microcontroller, giving you access to the vast library of Arduino I/O functionality. Our Arduino code is open and editable.

IO protocols

| WebSocket, ASCII TCP, REST, ASCII over Serial | Allow communication with the BB-400 to get and set values of IO lines over the local network or from the device itself. This is different to protocols that send data up to the cloud. | | |
|---|---|-------|-----------|
| | ASCII | REST | WebSocket |
| Max number of commands/sec | 400 | 150 | 350 |
| Average response time (for 1 user) | 2.7 ms | 11 ms | 2.5 ms |
| Max Number of simultaneous connections | 200 | n/a | 10 |
| Cloud Connectivity | Brainboxes are developing support for the following cloud platforms.... Amazon Web Services, Azure, Google cloud platform, IBM Watson Soon you will be able to stream data to these services simply by entering your credentials. You have the option to write and deploy your own connection to the cloud platform of your choice. | | |

UK +44 (0)151 220 2500 // USA +1 855 958 2502
 www.brainboxes.com // sales@brainboxes.com

Serial Port

| | |
|--------------------|---|
| Ports | 1x RS232, RS422/485 Full Duplex, or RS485 Half Duplex Software Selectable |
| Baud Rate | Any custom Baud rate between 300 - 921,600 Baud can be selected |
| Tx FIFO Size | 64 |
| Rx FIFO Size | 64 |
| Data Bits | 5,6,7 or 8 (1 stop bit) |
| Parity | Odd, Even, None |
| Stop Bits | 1, 1.5 or 2 |
| Flow Control | RTS/CTS, XON/XOFF |
| Operating Distance | RS422/485 Standard (4000 ft : 1200 metres) / EIA - RS232 Standard |
| Software | Manage Serial connections through the web admin interface. Alternatively use a program like Node-RED, or any programming language like python, C#, and bash. Code examples are available on our website. |
| Connect | Connect to weigh scales, PLCs, CNC machines, vibration sensors, barcode scanners, printers, scientific and medical equipment using the ubiquitous Serial port. Integrate a host of traditionally stand alone or legacy equipment into your networked smart factory. |

USB Port

| | |
|-------|--|
| Ports | 1x USB 2.0 Micro AB |
| | <p>Enclosed USB port for developer use.</p> <p>The BB-400 is a USB host, much like a regular computer. For example, files can be copied to and from a memory stick by logging in and using Linux commands to mount the memory stick as a drive inside the Pi.</p> <p>It is also possible to set the BB-400 to 'Flash' mode, by changing the jumper. Note this is only recommended in specific applications as doing so will reformat the device and wipe the Pi's image.</p> |

sales@brainboxes.com**Packaging Information**

| | |
|---------------------|-----------------------------------|
| Packaging | Quick Start Guide |
| Device | BB-400 + Antenna |
| Packaged Weight | 0.334 kg, 11.78 ounces |
| Packaged Dims | 160x135x49 mm, 6.3x5.3x1.9 inches |
| GTIN Universal Code | 837324004441 |

Approvals

| | |
|--------------------|--|
| Industry Approvals | Microsoft Certified Gold Partner, WEEE, RoHS, AEO (C-TPAT), CE, UKCA |
|--------------------|--|

Product Support

| | |
|----------|---|
| Warranty | Lifetime - online registration required |
| Support | Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team |

Additional Information

| | |
|--------------|--|
| Made In | Manufactured in the UK by Brainboxes |
| Customisable | Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users. More info: sales@brainboxes.com |

Raspberry Pi is a trademark of the Raspberry Pi Foundation.

Optional Accessories:

PW-400
12VDC power supply with connectors for UK, USA, EU and AUS mains socket. 'Tails' are suitable for connecting to screw terminal blocks.



MK-588
6 coloured PCB connectors. Individually numbered pins; 5 x 3.5mm pitch screw connections with tension sleeve.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Brainboxes:

BB-400