

Bulkhead

Adapter *2.4 mm-F to 2.4 mm-F*

24FPM-24F+

50Ω DC to 50 GHz

The Big Deal

- Ultra-wideband, DC-50 GHz
- Flat response
- Low insertion loss, 0.11 dB
- Excellent VSWR, 1.04:1



CASE STYLE: DJ3008

Product Overview

Mini-Circuits' 24FPM-24F+ is a wideband bulkhead adapter supporting a wide range of applications from DC to 50 GHz. This model provides excellent VSWR, low insertion loss, and flat response versus frequency. The 24FPM-24F+ features passivated stainless steel construction and measures only 0.77" in length.

Key Features

Feature	Advantages
Wideband, DC to 50 GHz	Wide frequency range provides application flexibility and makes this model ideal for broad-band and multi-band use.
Excellent VSWR, 1.04:1	Provides good matching for 50Ω systems and minimizes signal reflections across wide frequency range.
Low insertion loss, 0.11 dB	Provides excellent signal power transmission from input to output.
Passivated stainless steel construction.	Stands up to wear and tear in demanding environments and provides excellent reliability.
Very wide operating temperature range, -55 to +100°C	Withstands extreme operating conditions and is suitable for use near high power components where heat rise is common.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bulkhead Adapter

2.4 mm-F to 2.4 mm-F

50Ω DC to 50 GHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Features

- flat response
- excellent VSWR, 1.04 typ.
- low cost adapters, available from stock
- stainless steel body, passivated

Applications

- 5G mmW,
- KA/KU band
- Satellite Comm

24FPM-24F+



Generic photo used for illustration purposes only

CASE STYLE: DJ3008


Connectors	Model
2.4mm-Female	24FPM-24F+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Dimensions

inches [mm]





Electrical Specifications at 25°C

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		50	GHz
Insertion Loss	DC-10		0.05	0.2	dB
	10-20		0.08	0.2	
	20-40		0.11	0.2	
	40-50		0.13	0.25	
VSWR	DC-10		1.01	1.2	:1
	10-20		1.01	1.2	
	20-40		1.04	1.2	
	40-50		1.04	1.2	

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	
		2.4 mm-F	2.4 mm-F
10	0.01	1.02	1.02
100	0.01	1.00	1.00
500	0.02	1.01	1.01
2000	0.03	1.01	1.01
4000	0.05	1.02	1.02
6000	0.06	1.01	1.01
10000	0.06	1.01	1.01
15000	0.07	1.01	1.02
20000	0.09	1.03	1.04
25000	0.10	1.06	1.06
30000	0.10	1.01	1.02
35000	0.11	1.04	1.04
40000	0.11	1.01	1.03
46000	0.12	1.09	1.09
50000	0.16	1.09	1.09



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
ECO-001629
24FPM-24F+
GY/RS/CP
201029

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[24FPM-24F+](#)