

NCVT1XT NON-CONTACT VOLTAGE TESTER

Dustproof and waterproof with durable 3m drop protection



NCVT1XT

**TOUGH
METER**



UK
CA



CAT IV
1000V

- Provides non-contact detection of 70 to 1000V AC in cables, cords, circuit breakers, lighting fixtures, switches, non tamper-resistant outlets and wires
- Durable meter is dustproof and waterproof with an IP67 rating and 9.8-Foot (3 m) drop protection
- High intensity, bright green LED indicates the tester is powered on
- Lightweight compact design with a convenient clip to fit securely in your pocket
- Includes instructions and 2 x AAA 1.5 volt batteries
- Auto power-off feature conserves and extends battery life
- Low battery indicator
- Not recommended for testing tamper-resistant outlets; use Cat. Nos. NCVT-2P or NCVT-3P in low voltage mode



When voltage is detected, a high intensity, bright red LED illuminates and an audible tone will sound



Easy access to battery compartment



NCVT1XTKIT

Non-Contact Voltage and GFCI Receptacle Premium Test Kit

(Cat. No. NCVT1XTKIT) includes the NEW Non-Contact Voltage Tester (Cat. No. NCVT1XT) and a GFCI Receptacle Tester (Cat. No. RT210).

The GFCI Receptacle Tester (Cat. No. RT210) is designed to detect the most common wiring problems in standard and GFCI receptacles.

For Professionals
SINCE 1857™



Cat. No.	UPC	Description	Voltage	Batteries	Ingress Protection	Drop Protection
NCVT1XT	69383-0	Non-Contact Voltage Tester	70 to 1000V AC	2 x AAA	IP67	9.8' (3 m)
Kit						
NCVT1XTKIT	69390-8	Non-Contact Voltage and GFCI Receptacle Premium Test Kit	Includes: Cat. No. NCVT1XT Non-Contact Voltage Tester; Cat. No. RT210 GFCI Outlet Tester; Instructions; and All Required Batteries			

⚠ Visit www.kleintools.com for warnings and instructions.

See our complete line of Test and Measurement
www.kleintools.com



© 2022 Klein Tools, Inc.
Lincolnshire, IL 60069
MKT120922 Rev. 12/22 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Klein Tools:

[NCVT1XT](#) [NCVT1XTKIT](#)