



Coaxial Cable


50Ω 7 inch DC to 18 GHz

Maximum Ratings

Operating Temperature	-55°C to 105°C
Storage Temperature	-55°C to 105°C
Power Handling at 25°C, Sea Level	546W at 0.5 GHz 387W at 1 GHz 273W at 2 GHz 156W at 6 GHz 121W at 10 GHz 90W at 18 GHz

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing




* OVERALL CONNECTOR DIMENSION (CONNECTOR SHAPE MAY VARY)

Outline Dimensions (inch/mm)

A	B	C1	C2	D
7.00	0.88	0.750	0.375	0.88
177.80	22.352	19.05	9.53	22.35
E1	E2	F	T	wt
0.750	0.375	.163±.004	0.10	grams
19.05	9.53	4.14±0.10	2.54	70

Cable Construction



Connectors: Coupling Nut: Brass, Nickel Plated
Body: Brass, Nickel Plated
Center Pin: Brass, Gold Plated

Typical Bending Capability



Features

- Wideband frequency coverage, DC to 18 GHz
- Low Loss, 0.45 dB at 18 GHz
- Excellent Return Loss, 18 dB at 18 GHz
- Hand formable to almost any custom shape without special bending tools
- 8mm bend radius for tight installations
- Anti-torque nut prevents cable stress during installation
- Insulated outer jacket standard¹
- **Ideal for interconnect of assembled systems**

Applications

- Replacement for custom bent 0.141" semi-rigid cables
- Communication receivers and transmitters
- Military and aerospace system
- Environmental and test chambers



Electrical Specifications at 25°C

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		18	GHz
Length			7		Inches
Insertion Loss	DC - 2	—	0.08	0.32	dB
	2 - 6	—	0.11	0.58	
	6 - 12	—	0.21	0.77	
	12 - 18	—	0.46	1.07	
Return Loss	DC - 2	23	31	—	dB
	2 - 6	23	28	—	
	6 - 12	17	21	—	
	12 - 18	17	18	—	

1. Unjacketed cable also available upon request.
2. Custom sizes available, consult factory.

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		N-MALE	N-MALE
100	0.01	48.5	51.5
1000	0.02	43.8	44.8
1800	0.05	38.7	36.8
2500	0.13	33.9	33.9
4000	0.16	30.2	30.3
5000	0.18	38.5	42.5
6000	0.05	34.4	35.7
7000	0.21	45.4	51.5
8000	0.23	31.8	32.0
9000	0.25	26.8	26.8
10000	0.15	23.5	23.4
12000	0.30	31.6	32.5
14000	0.32	26.7	26.8
16000	0.35	28.3	27.0
18000	0.28	25.1	24.6



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Rev. B
M167677
141-7NM+
RK/CP/AM
180504

141-7NM+



CASE STYLE: KQ1637-7

Connectors	Model
N-Male	141-7NM+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[141-7NM+](#)