

Surface Mount Directional Coupler

75Ω 20 to 1000 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

INPUT	1
OUTPUT	6
COUPLED	3
GROUND	2
75Ω TERM EXTERNAL	4
ISOLATE (DO NOT USE)	5

Outline Drawing



PCB Land Pattern




Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch)

A	B	C	D	E	F	G
.272	.310	.220	.100	.112	.055	.100
6.91	7.87	5.59	2.54	2.84	1.40	2.54
H	J	K	L	M	N	O
.030	.026	.065	.300	.075	.050	.100
0.76	0.66	1.65	7.62	1.91	1.27	2.54
wt						grams
						0.20

Demo Board MCL P/N: TB-08 Suggested PCB Layout (PL-042)



- NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 3. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 4. DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- wideband, 20-1000 MHz
- low mainline loss, 0.4 dB typ.
- good directivity, 18 dB typ.
- excellent coupling flatness, ±0.15 dB typ.
- aqueous washable
- protected by U.S. Patents 6,133,525 & 6,140,887

Applications

- cable tv
- communications




Directional Coupler Electrical Specifications

FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)			DIRECTIVITY (dB)			VSWR (:1)	POWER INPUT, W	
	Nom.	Flatness	L	M	U	L	M	U		L	MU
f _L -f _U			Typ. Max.	Typ. Max.	Typ. Max.	Typ. Min.	Typ. Min.	Typ. Min.	Typ.	Max.	Max.
20-1000	17.4±0.5	±0.5	0.4 0.8	0.4 1.0	0.5 1.2	17 14	18 14	17 12	1.15	1.0	1.0


L= 20-200 MHz M= 200-500 MHz U= 500-1000 MHz
1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
20.60	0.41	17.38	17.05	25.15	26.01	19.37
35.30	0.37	17.41	17.17	26.48	29.41	21.55
50.00	0.35	17.38	17.23	27.69	31.77	22.76
225.00	0.36	17.35	17.74	28.16	31.23	26.30
400.00	0.40	17.37	17.93	24.88	24.39	30.25
492.00	0.43	17.41	17.78	22.40	21.78	33.74
630.00	0.46	17.46	17.33	20.56	19.28	44.74
768.00	0.51	17.53	16.72	19.50	18.43	34.24
895.00	0.56	17.57	16.33	19.13	18.15	27.95
1000.00	0.60	17.63	16.23	18.76	18.16	26.97



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. F
M158496
ED-6814/1
ADC-18-4-75+
WZ/TD/CP/AM
200414

ADC-18-4-75+



Generic photo used for illustration purposes only
CASE STYLE: CD542

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel
at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ADC-18-4-75+](#)