

Frequency Mixer

ADE-11X+

Level 7 (LO Power +7 dBm) 10 to 2000 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	6
RF	2
IF	3
GROUND	1,4,5

Outline Drawing



PCB Land Pattern




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.112	.055	.100
6.91	7.87	5.59	2.54	2.84	1.40	2.54

H	J	K	L	wt
.030	.026	.065	.300	grams
0.76	0.66	1.65	7.62	0.20

Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low conversion loss, 7.1 dB typ.
- excellent L-R isolation, 36 dB typ. & L-I isolation, 37 dB typ.
- low profile package
- aqueous washable
- protected by U.S. Patent 6,133,525

Applications

- cellular
- PCN
- VHF & UHF
- communication receivers & transmitters



Generic photo used for illustration purposes only
CASE STYLE: CD542

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			IP3 at center band (dBm)
LO/RF	IF	Mid-Band		Total Range Max.	L	M	U	L	M	U		
		$\bar{X}$	σ									
		Max.										
f_L - f_U					Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ.	
10-2000	5-1000	7.1	0.10	8.2	9.8	62 45	36 20	27 18	60 45	37 20	38 20	9

1 dB COMP: +1 dBm typ.


L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]







m = mid band [2f_L to f_U/2]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm
10.1	40.1	6.96	64.83	64.24	1.08	2.86
70.1	100.1	7.28	61.55	55.99	1.02	2.54
130.1	160.1	7.34	58.29	52.05	1.05	2.61
250.1	280.1	7.46	53.74	47.47	1.15	2.54
310.1	340.1	7.46	52.18	45.94	1.23	2.65
430.1	460.1	7.65	48.59	42.89	1.40	2.65
550.1	580.1	7.57	44.12	40.93	1.58	2.72
670.1	700.1	7.78	42.25	39.40	1.74	2.86
790.1	820.1	7.84	39.37	37.63	1.84	2.90
850.1	880.1	7.64	39.00	37.00	1.81	2.90
970.1	1000.1	7.43	36.19	36.87	1.76	3.09
1030.1	1060.1	7.47	35.41	36.35	1.73	3.18
1150.1	1180.1	7.62	34.28	35.45	1.74	3.29
1210.1	1240.1	7.93	34.68	34.87	1.81	3.37
1450.1	1480.1	7.88	32.49	35.07	1.61	3.16
1510.1	1540.1	7.81	30.67	35.52	1.58	3.24
1630.1	1660.1	7.86	28.65	36.47	1.49	3.43
1810.1	1840.1	8.31	26.47	35.66	1.35	3.82
1930.1	1960.1	8.76	25.40	35.41	1.25	3.99
2050.1	2080.1	9.42	24.27	32.47	1.21	4.23

Electrical Schematic





Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ADE-11X+](#)