

Surface Mount

Power Splitter/Combiner

ADP-2-20-75+ ADP-2-20-75

2 Way-0° 75Ω 5 to 2000 MHz



CASE STYLE: CD542

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost
 Reel Size Devices/Reel
 7" 10, 20, 50, 100, 200, 500
 13" 500, 1000

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	0.5W max.
Internal Dissipation	0.25W max.

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

SUM PORT	1
PORT 1	3
PORT 2	4
GROUND	6
NOT USED	2,5

Outline Drawing



PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.272	.310	.220	.100	.112	.055	.100
6.91	7.87	5.59	2.54	2.84	1.40	2.54

H	J	K	L	wt
.030	.026	.065	.300	grams
0.76	0.66	1.65	7.62	0.20

Demo Board MCL P/N: TB-243 Suggested PCB Layout (PL-141)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wide bandwidth, 5 to 2000 MHz
- low insertion loss, 0.5 dB typ.
- excellent amplitude unbalance, 0.05 dB typ.
- excellent phase unbalance, 0.5 deg. typ.
- aqueous washable
- protected under U.S. Patent 6,133,525

Applications

- instrumentation
- PCS/cellular

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)			INSERTION LOSS (dB) ABOVE 3.0 dB			PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)								
	L		M	U		L		M	U		L		M	U				
	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Max.				
f _c -f _u																		
5-2000	16	12	16	13	28	15	0.4	0.9	0.5	1.2	0.6	1.4	1.0	4.0	5.0	0.15	0.3	0.6

L = 5-50 MHz M = 50-1000 MHz U = 1000-2000 MHz

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
5.00	3.53	3.52	0.01	16.13	0.06	1.98	1.48	1.48
10.00	3.53	3.53	0.00	16.92	0.05	1.98	1.49	1.49
50.00	3.52	3.52	0.00	16.83	0.09	1.97	1.48	1.48
200.00	3.50	3.51	0.01	17.01	0.35	1.95	1.51	1.51
500.00	3.54	3.55	0.01	18.26	0.77	1.97	1.62	1.61
600.00	3.56	3.56	0.01	19.16	0.88	2.00	1.64	1.65
750.00	3.52	3.53	0.01	21.42	1.04	2.05	1.68	1.67
850.00	3.56	3.57	0.02	24.14	1.13	2.06	1.69	1.69
1000.00	3.55	3.56	0.02	32.31	1.20	2.05	1.72	1.71
1200.00	3.56	3.56	0.01	27.75	1.30	1.87	1.75	1.78
1300.00	3.57	3.58	0.01	23.96	1.24	1.74	1.77	1.81
1500.00	3.62	3.61	0.01	21.15	1.24	1.48	1.84	1.84
1700.00	3.68	3.66	0.03	22.76	1.07	1.18	1.82	1.84
1800.00	3.72	3.69	0.03	25.81	0.93	1.05	1.77	1.81
2000.00	3.79	3.73	0.06	21.22	0.36	1.29	1.64	1.62

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ADP-2-20-75+](#)