

Low Pass Filter

BLP-90+

50Ω DC to 81 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Features

- rugged shielded case
- other standard and custom BLP models available with wide selection of fco

Applications

- test equipment
- lab use
- video equipment



Generic photo used for illustration purposes only

CASE STYLE: FF55


Connectors Model

BNC BLP-90+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch/mm)

B	D	wt
.54	2.59	grams
13.72	65.79	40.0


Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-81	90	121-157 157-400	1.7 18

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
$\bar{x}$	σ			
1.00	0.05	0.1	1.00	9.672
12.50	0.14	0.1	12.50	9.503
24.00	0.18	0.1	24.00	9.491
35.50	0.31	0.1	35.50	9.776
46.50	0.42	0.1	46.50	10.240
58.00	0.43	0.1	58.00	11.244
81.00	0.69	0.1	81.00	15.573
87.00	1.28	0.4	84.00	17.894
90.00	2.01	0.5	87.00	19.997
93.00	6.43	0.9	90.00	24.263
97.00	8.74	1.0	93.00	21.734
104.01	12.94	1.1	97.00	17.532
111.00	16.72	1.2	104.00	15.893
115.52	21.91	1.2	111.00	12.218
121.03	26.16	1.2	115.50	5.804
130.03	32.40	1.3	121.00	5.229
140.04	38.50	1.4	130.00	3.892
145.04	41.31	1.4	135.00	2.740
150.04	43.98	1.5	140.00	0.487
155.05	46.76	1.7	145.00	0.841
157.05	47.69	1.8	150.00	2.060
184.06	60.11	2.9	155.00	7.687
206.57	66.87	1.4	157.00	5.680
229.58	75.03	5.6	184.00	5.380
252.57	74.83	7.6	195.50	5.060
298.08	76.96	7.1	206.50	4.740
321.08	75.07	4.9	218.00	4.320
355.57	73.10	4.4	229.50	4.010
378.08	75.50	4.8	241.00	3.760
400.07	74.56	6.3	252.50	3.450



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[BLP-90+](#)