

Surface Mount

Bandpass Filter

BPF-C650+

50Ω 560 to 780 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

INPUT	2
OUTPUT	9
NOT CONNECTED	6, 13
GROUND	1, 3, 4, 5, 7, 8, 10, 11, 12, 14

Outline Drawing




Outline Dimensions (inch mm)


A	B	C	D	E	G	H	J	K	M	N	wt.
.870	.800	.25	.100	.097	.060	.040	.105	.910	.060	.060	grams
22.10	20.32	6.35	2.54	2.46	1.52	1.02	2.67	23.11	1.52	1.52	2.85

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-500+
Suggested PCB Layout (PL-294)



Notes:
1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B, DIELECTRIC THICKNESS: .030±.002"; COPPER: 1/2 OZ EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



Features

- Flat group delay
- High rejection
- Shielded case
- Aqueous washable

Applications

- Receivers / transmitters
- Wireless communication systems



Generic photo used for illustration purposes only
CASE STYLE: HU1186


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 3dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
650	560 - 780	280	890	185	920 - 1600	1.4	1.8	18

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	$\bar{x}$	σ			
2.0	101.98	9.04	0.00	560.0	3.18
100.0	74.01	0.79	0.11	570.0	3.11
185.0	48.87	0.16	0.24	580.0	3.06
280.0	29.90	0.14	0.35	600.0	3.00
340.0	19.49	0.15	0.54	610.0	2.96
400.0	10.25	0.17	1.40	630.0	2.94
450.0	5.12	0.09	3.06	640.0	2.94
500.0	2.23	0.06	6.40	650.0	2.99
520.0	1.53	0.05	8.96	660.0	3.07
560.0	0.82	0.01	17.93	680.0	3.25
650.0	0.75	0.02	16.06	700.0	3.35
780.0	1.16	0.04	19.23	710.0	3.41
820.0	2.80	0.14	8.88	720.0	3.51
830.0	5.62	0.24	4.20	730.0	3.64
847.0	13.23	0.39	1.37	740.0	3.86
890.0	33.65	0.40	0.47	750.0	4.15
920.0	51.96	0.95	0.36	770.0	4.79
1600.0	53.63	1.11	0.19	780.0	5.21



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[BPF-C650+](#)